

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P563321

Luminaire Tested: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P563321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD
Description: 2X4 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7455.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 70.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563321

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P563321

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	106	102	99		108	104	100	97		100	97	94		96	94	91		92	90	89
2	101	94	88	83		99	92	87	82		89	84	80		86	82	78		83	79	77
3	93	84	77	71		91	82	76	70		79	74	69		77	72	68		74	70	67
4	86	75	67	61		84	74	66	61		72	65	60		69	64	59		67	62	58
5	80	68	60	54		78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	48		72	61	53	47		59	52	47		57	51	47		56	50	46
7	69	56	48	43		67	56	48	42		54	47	42		53	46	42		51	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	61	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	37	32		43	36	32		42	36	32		41	36	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5109	5109	5109
5°	5040	5034	5028
10°	4996	4990	4954
15°	4862	4813	4746
20°	4683	4608	4482
25°	4491	4393	4119
30°	4256	4120	3710
35°	4031	3807	3432
40°	3801	3470	3123
45°	3584	3208	2824
50°	3317	2977	2518
55°	3069	2698	2255
60°	2812	2410	2020
65°	2474	2110	1789
70°	2038	1848	1520
75°	1620	1415	1484
80°	1089	1020	952
85°	678	814	949

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3584 cd/sqm

TEST NUMBER: P563321

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.5	4.7
10°-20°	970.1	13.0
20°-30°	1343.1	18.0
30°-40°	1432.1	19.2
40°-50°	1306.5	17.5
50°-60°	1023.5	13.7
60°-70°	667.1	8.9
70°-80°	295.5	4.0
80°-90°	63.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2666.7	35.8
0°-40°	4098.8	55.0
0°-60°	6428.9	86.2
0°-90°	7455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7455.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3798	3798	3798	3798	3798	
5°	3732	3727	3727	3723	3723	354
15°	3490	3490	3455	3420	3407	981
25°	3025	3007	2959	2854	2775	1389
35°	2454	2436	2318	2142	2090	1534
45°	1883	1844	1686	1545	1484	1451
55°	1308	1269	1150	1014	961	1173
65°	777	733	663	676	562	766
75°	312	290	272	259	285	334
85°	44	48	53	57	62	61
90°	0	0	0	0	0	

TEST NUMBER: P563321

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-80-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3797.5	3797.5	3797.5	3797.5	3797.5
2.5°	3771.1	3771.1	3771.1	3766.7	3766.7
5°	3731.6	3727.2	3727.2	3722.8	3722.8
7.5°	3700.9	3696.5	3692.1	3687.7	3678.9
10°	3657.0	3657.0	3652.6	3630.7	3626.3
12.5°	3586.8	3582.4	3564.8	3534.1	3525.3
15°	3490.2	3490.2	3455.0	3419.9	3406.8
17.5°	3384.8	3380.4	3336.5	3301.4	3283.8
20°	3270.7	3261.9	3218.0	3160.9	3130.2
22.5°	3143.3	3143.3	3090.7	3016.0	2985.3
25°	3024.8	3007.3	2959.0	2853.6	2774.6
27.5°	2888.7	2862.4	2809.7	2660.4	2568.2
30°	2739.5	2726.3	2651.6	2458.5	2388.2
32.5°	2599.0	2577.0	2498.0	2296.0	2239.0
35°	2454.1	2436.5	2318.0	2142.4	2089.7
37.5°	2309.2	2287.3	2138.0	1997.5	1931.7
40°	2164.3	2138.0	1975.6	1848.3	1778.0
42.5°	2028.2	1993.1	1835.1	1699.0	1620.0
45°	1883.4	1843.9	1685.8	1545.3	1483.9
47.5°	1738.5	1703.4	1558.5	1413.6	1343.4
50°	1584.8	1554.1	1422.4	1277.5	1202.9
52.5°	1457.5	1409.2	1281.9	1137.0	1075.6
55°	1308.3	1268.8	1150.2	1014.1	961.4
57.5°	1172.2	1132.7	1022.9	895.6	851.7
60°	1044.9	987.8	895.6	785.8	750.7
62.5°	904.4	860.5	781.4	689.3	733.2
65°	777.1	733.2	662.9	676.1	561.9
67.5°	636.6	614.6	553.2	491.7	474.1
70°	518.0	491.7	469.7	403.9	386.3
72.5°	412.7	386.3	355.6	320.5	307.3
75°	311.7	289.7	272.2	259.0	285.4
77.5°	215.1	206.3	193.2	180.0	175.6
80°	140.5	136.1	131.7	127.3	122.9
82.5°	83.4	83.4	83.4	83.4	83.4
85°	43.9	48.3	52.7	57.1	61.5
87.5°	26.3	26.3	30.7	35.1	39.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)