

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P554210

Luminaire Tested: **FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P554210  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90  
Description: 2FT FUSL SURFACE MOUNT WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .187 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1012.0 lumens  
Efficiency: N/A  
Efficacy: 86.5 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26  
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P554210

CATALOG NUMBER: FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P554210

CATALOG NUMBER: FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2356	2356	2356
5°	2362	2352	2332
10°	2337	2330	2303
15°	2295	2295	2269
20°	2247	2250	2220
25°	2173	2200	2165
30°	2046	2138	2112
35°	1933	2049	2053
40°	1839	1938	1989
45°	1734	1821	1914
50°	1623	1716	1833
55°	1498	1597	1734
60°	1349	1457	1612
65°	1191	1295	1467
70°	993	1103	1246
75°	780	882	975
80°	558	620	688
85°	364	364	340



TEST NUMBER: P554210

CATALOG NUMBER: FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.2	4.1
10°-20°	115.8	11.4
20°-30°	169.2	16.7
30°-40°	192.0	19.0
40°-50°	185.4	18.3
50°-60°	152.9	15.1
60°-70°	101.8	10.1
70°-80°	45.6	4.5
80°-90°	8.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.1	32.2
0°-40°	518.2	51.2
0°-60°	856.5	84.6
0°-90°	1012.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1012.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	438	438	438	438	438	
5°	437	437	435	433	432	41
15°	412	413	412	410	407	116
25°	366	369	370	368	364	168
35°	294	298	312	314	312	184
45°	228	232	239	250	252	176
55°	160	162	170	180	185	142
65°	94	96	102	109	115	93
75°	38	40	42	44	47	41
85°	6	6	6	6	6	8
90°	0	0	0	0	0	



TEST NUMBER: P554210

CATALOG NUMBER: FUSL-12-2-LD4-1LO-35-UNV-93-85-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	437.7	437.7	437.7	437.7	437.7
2.5°	438.8	439.0	438.0	435.3	433.6
5°	437.2	437.0	435.3	433.0	431.6
7.5°	432.3	432.6	432.1	428.8	426.9
10°	427.6	427.7	426.4	423.7	421.5
12.5°	421.5	421.4	419.5	418.2	414.6
15°	411.9	412.9	411.9	410.1	407.2
17.5°	402.7	402.7	403.4	400.2	398.0
20°	392.3	392.8	392.8	390.2	387.7
22.5°	380.2	381.7	382.2	379.5	376.5
25°	365.9	368.7	370.4	367.7	364.5
27.5°	348.6	352.9	358.0	355.9	352.4
30°	329.2	335.6	344.0	342.3	339.8
32.5°	310.9	317.3	328.9	328.2	326.9
35°	294.2	298.3	311.9	313.6	312.4
37.5°	278.4	282.1	294.9	298.8	297.8
40°	261.8	265.8	275.9	282.8	283.1
42.5°	245.3	249.2	257.4	267.3	267.3
45°	227.8	231.7	239.3	250.2	251.5
47.5°	210.7	214.7	222.1	233.0	235.2
50°	193.9	197.6	205.0	215.6	218.9
52.5°	176.4	180.4	187.6	197.4	202.3
55°	159.6	162.3	170.2	179.6	184.8
57.5°	142.1	144.6	153.5	161.6	167.0
60°	125.3	128.5	135.4	143.6	149.8
62.5°	109.1	112.5	118.4	125.6	132.7
65°	93.5	96.0	101.7	109.0	115.2
67.5°	78.4	80.5	86.3	91.3	97.9
70°	63.1	65.9	70.1	75.0	79.2
72.5°	50.8	52.0	55.5	59.0	63.4
75°	37.5	39.5	42.4	44.4	46.9
77.5°	26.9	28.1	29.8	31.4	33.8
80°	18.0	18.5	20.0	20.3	22.2
82.5°	10.9	11.3	11.6	11.8	12.4
85°	5.9	5.9	5.9	5.5	5.5
87.5°	3.4	3.4	2.9	2.4	1.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)