

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P556542

Luminaire Tested: **FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P556542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90  
Description: 4FT FUSL SURFACE MOUNT WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND  
.375 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND  
4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2175.0 lumens  
Efficiency: N/A  
Efficacy: 92.9 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P556542

CATALOG NUMBER: FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P556542

CATALOG NUMBER: FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2531	2531	2531
5°	2538	2527	2506
10°	2511	2504	2475
15°	2466	2466	2438
20°	2414	2417	2386
25°	2335	2364	2326
30°	2199	2298	2269
35°	2077	2202	2206
40°	1976	2083	2138
45°	1863	1957	2057
50°	1744	1844	1970
55°	1609	1716	1863
60°	1449	1566	1733
65°	1279	1392	1576
70°	1066	1186	1339
75°	838	947	1048
80°	600	666	739
85°	389	389	367



TEST NUMBER: P556542

CATALOG NUMBER: FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.6	4.1
10°-20°	248.8	11.4
20°-30°	363.6	16.7
30°-40°	412.7	19.0
40°-50°	398.4	18.3
50°-60°	328.6	15.1
60°-70°	218.9	10.1
70°-80°	97.9	4.5
80°-90°	17.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.9	32.2
0°-40°	1113.6	51.2
0°-60°	1840.7	84.6
0°-90°	2175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2175.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	940	939	936	930	928	89
15°	885	888	885	881	875	250
25°	786	792	796	790	783	360
35°	632	641	670	674	671	396
45°	490	498	514	538	541	378
55°	343	349	366	386	397	306
65°	201	206	219	234	248	199
75°	81	85	91	95	101	88
85°	13	13	13	12	12	17
90°	0	0	0	0	0	



TEST NUMBER: P556542

CATALOG NUMBER: FUSL-12-4-LD4-1LO-40-UNV-80-97-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	943.2	943.5	941.4	935.6	932.0
5°	939.5	939.2	935.6	930.5	927.6
7.5°	929.1	929.8	928.7	921.5	917.5
10°	918.9	919.3	916.4	910.6	905.9
12.5°	905.9	905.6	901.6	898.7	891.1
15°	885.3	887.5	885.3	881.4	875.2
17.5°	865.5	865.5	866.9	860.0	855.3
20°	843.1	844.1	844.1	838.7	833.3
22.5°	817.0	820.3	821.4	815.6	809.1
25°	786.3	792.5	796.1	790.3	783.4
27.5°	749.1	758.5	769.3	765.0	757.4
30°	707.6	721.3	739.4	735.7	730.3
32.5°	668.2	681.9	706.8	705.4	702.5
35°	632.4	641.1	670.3	673.9	671.4
37.5°	598.4	606.4	633.8	642.1	640.0
40°	562.6	571.3	593.0	607.8	608.5
42.5°	527.2	535.5	553.2	574.6	574.6
45°	489.6	498.0	514.2	537.7	540.6
47.5°	452.8	461.5	477.4	500.9	505.5
50°	416.7	424.6	440.5	463.3	470.5
52.5°	379.1	387.7	403.3	424.2	434.7
55°	342.9	348.7	365.7	385.9	397.1
57.5°	305.4	310.8	329.9	347.3	358.8
60°	269.2	276.1	290.9	308.6	322.0
62.5°	234.5	241.8	254.4	269.9	285.1
65°	200.9	206.3	218.6	234.2	247.5
67.5°	168.4	173.1	185.4	196.2	210.3
70°	135.5	141.7	150.7	161.2	170.2
72.5°	109.1	111.7	119.3	126.8	136.2
75°	80.6	84.9	91.1	95.4	100.8
77.5°	57.8	60.3	64.0	67.6	72.6
80°	38.7	39.8	43.0	43.7	47.7
82.5°	23.5	24.2	24.9	25.3	26.7
85°	12.6	12.6	12.6	11.9	11.9
87.5°	7.2	7.2	6.1	5.1	3.6
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)