

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P556361

Luminaire Tested: **FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P556361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD
Description: 4FT FUSL SURFACE MOUNT WITH .156 CLEAR PC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3630.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P556361

CATALOG NUMBER: FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P556361

CATALOG NUMBER: FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4225	4225	4225
5°	4236	4218	4182
10°	4191	4179	4132
15°	4116	4116	4069
20°	4029	4035	3983
25°	3897	3945	3882
30°	3669	3834	3787
35°	3467	3675	3681
40°	3299	3477	3568
45°	3110	3266	3433
50°	2911	3078	3287
55°	2685	2863	3110
60°	2418	2613	2892
65°	2135	2323	2630
70°	1780	1979	2235
75°	1398	1580	1750
80°	1000	1113	1234
85°	651	651	614



TEST NUMBER: P556361

CATALOG NUMBER: FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	4.1
10°-20°	415.2	11.4
20°-30°	606.8	16.7
30°-40°	688.8	19.0
40°-50°	664.9	18.3
50°-60°	548.5	15.1
60°-70°	365.3	10.1
70°-80°	163.4	4.5
80°-90°	29.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.8	32.2
0°-40°	1858.6	51.2
0°-60°	3072.0	84.6
0°-90°	3630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3630.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1570	1570	1570	1570	1570	
5°	1568	1568	1561	1553	1548	148
15°	1478	1481	1478	1471	1461	417
25°	1312	1323	1329	1319	1308	601
35°	1055	1070	1119	1125	1121	661
45°	817	831	858	897	902	631
55°	572	582	610	644	663	511
65°	335	344	365	391	413	332
75°	134	142	152	159	168	147
85°	21	21	21	20	20	28
90°	0	0	0	0	0	



TEST NUMBER: P556361

CATALOG NUMBER: FUSL-12-4-LD4-1HI-50-UNV-81-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1574.1	1574.7	1571.1	1561.4	1555.4
5°	1568.1	1567.5	1561.4	1553.0	1548.2
7.5°	1550.6	1551.8	1550.0	1537.9	1531.3
10°	1533.7	1534.3	1529.5	1519.8	1512.0
12.5°	1512.0	1511.4	1504.7	1499.9	1487.3
15°	1477.6	1481.2	1477.6	1471.0	1460.7
17.5°	1444.4	1444.4	1446.8	1435.4	1427.5
20°	1407.0	1408.9	1408.9	1399.8	1390.8
22.5°	1363.6	1369.0	1370.9	1361.2	1350.4
25°	1312.4	1322.6	1328.6	1319.0	1307.5
27.5°	1250.2	1265.9	1284.0	1276.8	1264.1
30°	1180.9	1203.8	1234.0	1227.9	1218.9
32.5°	1115.1	1138.1	1179.7	1177.3	1172.4
35°	1055.4	1069.9	1118.8	1124.8	1120.6
37.5°	998.7	1012.0	1057.8	1071.7	1068.1
40°	939.0	953.5	989.7	1014.4	1015.6
42.5°	879.9	893.8	923.4	958.9	958.9
45°	817.2	831.1	858.2	897.4	902.2
47.5°	755.7	770.2	796.7	835.9	843.7
50°	695.4	708.6	735.2	773.2	785.2
52.5°	632.7	647.1	673.1	708.0	725.5
55°	572.3	582.0	610.3	644.1	662.8
57.5°	509.6	518.7	550.6	579.6	598.9
60°	449.3	460.8	485.5	515.1	537.4
62.5°	391.4	403.5	424.6	450.5	475.8
65°	335.3	344.4	364.9	390.8	413.1
67.5°	281.0	288.9	309.4	327.5	351.0
70°	226.2	236.4	251.5	269.0	284.1
72.5°	182.1	186.4	199.0	211.7	227.4
75°	134.5	141.7	152.0	159.2	168.3
77.5°	96.5	100.7	106.7	112.8	121.2
80°	64.5	66.3	71.8	73.0	79.6
82.5°	39.2	40.4	41.6	42.2	44.6
85°	21.1	21.1	21.1	19.9	19.9
87.5°	12.1	12.1	10.3	8.4	6.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)