

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P557519

Luminaire Tested: **FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P557519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD  
Description: 4FT FUSL SURFACE MOUNT WITH .156 CLEAR PC FIXTURE SIDE AND .375  
CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 3500K CCT  
LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6522.0 lumens  
Efficiency: N/A  
Efficacy: 97.9 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P557519

CATALOG NUMBER: FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD

### Luminous Intensity Polar Plot





TEST NUMBER: P557519

CATALOG NUMBER: FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7590	7590	7590
5°	7610	7578	7514
10°	7530	7509	7423
15°	7396	7396	7312
20°	7239	7249	7156
25°	7001	7088	6975
30°	6593	6889	6805
35°	6229	6603	6614
40°	5927	6247	6410
45°	5588	5868	6169
50°	5231	5530	5906
55°	4824	5145	5587
60°	4345	4695	5196
65°	3836	4174	4727
70°	3197	3556	4016
75°	2512	2839	3143
80°	1796	1998	2216
85°	1170	1170	1105



TEST NUMBER: P557519

CATALOG NUMBER: FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	265.6	4.1
10°-20°	746.1	11.4
20°-30°	1090.2	16.7
30°-40°	1237.5	19.0
40°-50°	1194.7	18.3
50°-60°	985.5	15.1
60°-70°	656.3	10.1
70°-80°	293.7	4.5
80°-90°	52.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2101.9	32.2
0°-40°	3339.4	51.2
0°-60°	5519.5	84.6
0°-90°	6522.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6522.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2821	2821	2821	2821	2821	
5°	2817	2816	2805	2790	2782	267
15°	2655	2661	2655	2643	2624	748
25°	2358	2376	2387	2370	2349	1080
35°	1896	1922	2010	2021	2013	1188
45°	1468	1493	1542	1612	1621	1133
55°	1028	1046	1097	1157	1191	918
65°	602	619	656	702	742	597
75°	242	255	273	286	302	264
85°	38	38	38	36	36	51
90°	0	0	0	0	0	



TEST NUMBER: P557519

CATALOG NUMBER: FUSL-12-4-LD4-2STD-35-UNV-81-97-EDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2820.6	2820.6	2820.6	2820.6	2820.6
2.5°	2828.2	2829.3	2822.8	2805.4	2794.6
5°	2817.3	2816.3	2805.4	2790.3	2781.6
7.5°	2785.9	2788.1	2784.8	2763.2	2751.2
10°	2755.6	2756.7	2748.0	2730.7	2716.6
12.5°	2716.6	2715.5	2703.6	2694.9	2672.1
15°	2654.8	2661.3	2654.8	2642.9	2624.5
17.5°	2595.2	2595.2	2599.5	2579.0	2564.9
20°	2528.0	2531.3	2531.3	2515.0	2498.8
22.5°	2450.0	2459.8	2463.0	2445.7	2426.2
25°	2357.9	2376.3	2387.2	2369.8	2349.2
27.5°	2246.3	2274.5	2307.0	2294.0	2271.2
30°	2121.7	2162.9	2217.0	2206.2	2189.9
32.5°	2003.6	2044.7	2119.5	2115.2	2106.5
35°	1896.3	1922.3	2010.1	2020.9	2013.3
37.5°	1794.4	1818.3	1900.6	1925.5	1919.0
40°	1687.2	1713.2	1778.2	1822.6	1824.8
42.5°	1581.0	1605.9	1659.0	1722.9	1722.9
45°	1468.3	1493.2	1542.0	1612.4	1621.1
47.5°	1357.7	1383.8	1431.4	1501.9	1515.9
50°	1249.4	1273.2	1320.9	1389.2	1410.8
52.5°	1136.7	1162.7	1209.3	1272.1	1303.6
55°	1028.3	1045.7	1096.6	1157.3	1190.9
57.5°	915.6	931.9	989.3	1041.3	1076.0
60°	807.3	827.9	872.3	925.4	965.5
62.5°	703.3	724.9	762.9	809.4	855.0
65°	602.5	618.7	655.6	702.2	742.3
67.5°	505.0	519.0	555.9	588.4	630.7
70°	406.3	424.8	451.9	483.3	510.4
72.5°	327.2	334.8	357.6	380.3	408.5
75°	241.6	254.6	273.1	286.1	302.3
77.5°	173.4	181.0	191.8	202.6	217.8
80°	115.9	119.2	128.9	131.1	143.0
82.5°	70.4	72.6	74.8	75.9	80.2
85°	37.9	37.9	37.9	35.8	35.8
87.5°	21.7	21.7	18.4	15.2	10.8
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)