

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P557608

Luminaire Tested: **FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P557608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90  
Description: 4FT FUSL SURFACE MOUNT WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5158.0 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P557608

CATALOG NUMBER: FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P557608

CATALOG NUMBER: FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6003	6003	6003
5°	6019	5993	5942
10°	5955	5939	5870
15°	5849	5849	5782
20°	5725	5733	5659
25°	5537	5605	5516
30°	5214	5448	5381
35°	4927	5222	5231
40°	4687	4940	5069
45°	4419	4641	4879
50°	4137	4374	4671
55°	3816	4069	4419
60°	3436	3713	4110
65°	3034	3301	3738
70°	2529	2812	3175
75°	1987	2246	2486
80°	1421	1581	1753
85°	926	926	874



TEST NUMBER: P557608

CATALOG NUMBER: FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.0	4.1
10°-20°	590.0	11.4
20°-30°	862.2	16.7
30°-40°	978.7	19.0
40°-50°	944.8	18.3
50°-60°	779.4	15.1
60°-70°	519.0	10.1
70°-80°	232.3	4.5
80°-90°	41.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1662.3	32.2
0°-40°	2641.0	51.2
0°-60°	4365.2	84.6
0°-90°	5158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5158.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2231	2231	2231	2231	2231	
5°	2228	2227	2219	2207	2200	211
15°	2100	2105	2100	2090	2076	592
25°	1865	1879	1888	1874	1858	854
35°	1500	1520	1590	1598	1592	940
45°	1161	1181	1220	1275	1282	896
55°	813	827	867	915	942	726
65°	476	489	518	555	587	472
75°	191	201	216	226	239	209
85°	30	30	30	28	28	40
90°	0	0	0	0	0	



TEST NUMBER: P557608

CATALOG NUMBER: FUSL-12-4-LD4-2STD-40-UNV-93-88-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2230.7	2230.7	2230.7	2230.7	2230.7
2.5°	2236.7	2237.6	2232.4	2218.7	2210.1
5°	2228.1	2227.3	2218.7	2206.7	2199.9
7.5°	2203.3	2205.0	2202.4	2185.3	2175.9
10°	2179.3	2180.1	2173.3	2159.6	2148.4
12.5°	2148.4	2147.6	2138.1	2131.3	2113.3
15°	2099.6	2104.7	2099.6	2090.2	2075.6
17.5°	2052.5	2052.5	2055.9	2039.6	2028.5
20°	1999.3	2001.9	2001.9	1989.0	1976.2
22.5°	1937.6	1945.3	1947.9	1934.2	1918.8
25°	1864.8	1879.3	1887.9	1874.2	1857.9
27.5°	1776.5	1798.8	1824.5	1814.2	1796.2
30°	1678.0	1710.5	1753.4	1744.8	1731.9
32.5°	1584.5	1617.1	1676.2	1672.8	1666.0
35°	1499.7	1520.3	1589.7	1598.3	1592.3
37.5°	1419.1	1438.0	1503.1	1522.8	1517.7
40°	1334.3	1354.9	1406.3	1441.4	1443.1
42.5°	1250.3	1270.0	1312.0	1362.6	1362.6
45°	1161.2	1180.9	1219.5	1275.2	1282.0
47.5°	1073.8	1094.4	1132.1	1187.8	1198.9
50°	988.1	1006.9	1044.7	1098.6	1115.8
52.5°	899.0	919.5	956.4	1006.1	1030.9
55°	813.3	827.0	867.3	915.2	941.8
57.5°	724.1	737.0	782.4	823.6	851.0
60°	638.4	654.7	689.9	731.9	763.6
62.5°	556.2	573.3	603.3	640.2	676.2
65°	476.5	489.3	518.5	555.3	587.0
67.5°	399.3	410.5	439.6	465.3	498.8
70°	321.4	335.9	357.4	382.2	403.6
72.5°	258.8	264.8	282.8	300.8	323.1
75°	191.1	201.4	216.0	226.2	239.1
77.5°	137.1	143.1	151.7	160.3	172.3
80°	91.7	94.3	102.0	103.7	113.1
82.5°	55.7	57.4	59.1	60.0	63.4
85°	30.0	30.0	30.0	28.3	28.3
87.5°	17.1	17.1	14.6	12.0	8.6
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)