

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P557388

Luminaire Tested: **FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P557388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90
Description: 4FT FUSL SURFACE MOUNT WITH .156 CLEAR PC FIXTURE SIDE AND .250 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4513.9 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P557388

CATALOG NUMBER: FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P557388

CATALOG NUMBER: FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5253	5253	5253
5°	5267	5245	5200
10°	5211	5197	5138
15°	5119	5119	5060
20°	5011	5017	4952
25°	4845	4906	4828
30°	4563	4768	4710
35°	4312	4570	4578
40°	4102	4323	4437
45°	3867	4061	4270
50°	3620	3827	4088
55°	3339	3561	3867
60°	3007	3249	3596
65°	2655	2889	3271
70°	2212	2460	2779
75°	1738	1965	2175
80°	1243	1382	1534
85°	809	809	763



TEST NUMBER: P557388

CATALOG NUMBER: FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	4.1
10°-20°	516.4	11.4
20°-30°	754.6	16.7
30°-40°	856.5	19.0
40°-50°	826.8	18.3
50°-60°	682.1	15.1
60°-70°	454.2	10.1
70°-80°	203.2	4.5
80°-90°	36.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.7	32.2
0°-40°	2311.3	51.2
0°-60°	3820.2	84.6
0°-90°	4513.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4513.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1952	1952	1952	1952	1952	
5°	1950	1949	1942	1931	1925	185
15°	1837	1842	1837	1829	1816	518
25°	1632	1645	1652	1640	1626	747
35°	1312	1330	1391	1399	1394	822
45°	1016	1034	1067	1116	1122	784
55°	712	724	759	801	824	635
65°	417	428	454	486	514	413
75°	167	176	189	198	209	183
85°	26	26	26	25	25	35
90°	0	0	0	0	0	



TEST NUMBER: P557388

CATALOG NUMBER: FUSL-12-4-LD4-2LO-50-UNV-81-96-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.2	1952.2	1952.2	1952.2	1952.2
2.5°	1957.4	1958.2	1953.7	1941.7	1934.2
5°	1949.9	1949.2	1941.7	1931.2	1925.2
7.5°	1928.2	1929.7	1927.4	1912.4	1904.2
10°	1907.2	1907.9	1901.9	1889.9	1880.2
12.5°	1880.2	1879.4	1871.2	1865.2	1849.4
15°	1837.4	1841.9	1837.4	1829.2	1816.4
17.5°	1796.2	1796.2	1799.2	1784.9	1775.2
20°	1749.7	1751.9	1751.9	1740.7	1729.4
22.5°	1695.7	1702.4	1704.7	1692.7	1679.2
25°	1631.9	1644.7	1652.2	1640.2	1625.9
27.5°	1554.7	1574.2	1596.7	1587.7	1572.0
30°	1468.5	1497.0	1534.5	1527.0	1515.7
32.5°	1386.7	1415.2	1467.0	1464.0	1458.0
35°	1312.5	1330.5	1391.2	1398.7	1393.5
37.5°	1242.0	1258.5	1315.5	1332.7	1328.2
40°	1167.7	1185.7	1230.7	1261.5	1263.0
42.5°	1094.2	1111.5	1148.2	1192.5	1192.5
45°	1016.2	1033.5	1067.2	1116.0	1122.0
47.5°	939.7	957.7	990.7	1039.5	1049.2
50°	864.7	881.2	914.2	961.5	976.5
52.5°	786.7	804.7	837.0	880.5	902.2
55°	711.7	723.7	759.0	801.0	824.2
57.5°	633.7	645.0	684.7	720.7	744.7
60°	558.7	573.0	603.7	640.5	668.2
62.5°	486.7	501.7	528.0	560.2	591.7
65°	417.0	428.2	453.7	486.0	513.7
67.5°	349.5	359.2	384.7	407.2	436.5
70°	281.2	294.0	312.7	334.5	353.2
72.5°	226.5	231.7	247.5	263.2	282.7
75°	167.2	176.2	189.0	198.0	209.2
77.5°	120.0	125.2	132.7	140.2	150.7
80°	80.2	82.5	89.2	90.7	99.0
82.5°	48.7	50.2	51.7	52.5	55.5
85°	26.2	26.2	26.2	24.7	24.7
87.5°	15.0	15.0	12.7	10.5	7.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)