

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P557648

Luminaire Tested: **FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P557648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90
Description: 4FT FUSL SURFACE MOUNT WITH .187 CLEAR PC FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5970.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P557648

CATALOG NUMBER: FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P557648

CATALOG NUMBER: FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	50	47																			
6	73	60	51	45	71	59	51	45	57	50	45	56	49	44	54	48	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	49	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34																			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	33	29	28																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6948	6948	6948
5°	6966	6937	6878
10°	6892	6873	6795
15°	6770	6770	6693
20°	6627	6635	6550
25°	6408	6488	6385
30°	6035	6306	6229
35°	5702	6044	6054
40°	5425	5718	5867
45°	5115	5371	5647
50°	4788	5062	5406
55°	4416	4709	5114
60°	3977	4297	4757
65°	3512	3821	4326
70°	2927	3254	3676
75°	2300	2599	2877
80°	1644	1829	2029
85°	1071	1071	1010



TEST NUMBER: P557648

CATALOG NUMBER: FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.1	4.1
10°-20°	682.9	11.4
20°-30°	998.0	16.7
30°-40°	1132.8	19.0
40°-50°	1093.5	18.3
50°-60°	902.1	15.1
60°-70°	600.7	10.1
70°-80°	268.8	4.5
80°-90°	48.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1924.0	32.2
0°-40°	3056.8	51.2
0°-60°	5052.4	84.6
0°-90°	5970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5970.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2582	2582	2582	2582	2582	
5°	2579	2578	2568	2554	2546	244
15°	2430	2436	2430	2419	2402	685
25°	2158	2175	2185	2169	2150	988
35°	1736	1760	1840	1850	1843	1088
45°	1344	1367	1411	1476	1484	1037
55°	941	957	1004	1059	1090	840
65°	552	566	600	643	679	547
75°	221	233	250	262	277	242
85°	35	35	35	33	33	47
90°	0	0	0	0	0	



TEST NUMBER: P557648

CATALOG NUMBER: FUSL-12-4-LD4-2STD-50-UNV-82-84-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2581.9	2581.9	2581.9	2581.9	2581.9
2.5°	2588.8	2589.8	2583.9	2568.0	2558.1
5°	2578.9	2577.9	2568.0	2554.1	2546.2
7.5°	2550.1	2552.1	2549.1	2529.3	2518.4
10°	2522.4	2523.3	2515.4	2499.5	2486.7
12.5°	2486.7	2485.7	2474.7	2466.8	2446.0
15°	2430.1	2436.1	2430.1	2419.2	2402.3
17.5°	2375.6	2375.6	2379.5	2360.7	2347.8
20°	2314.1	2317.0	2317.0	2302.2	2287.3
22.5°	2242.6	2251.6	2254.5	2238.7	2220.8
25°	2158.3	2175.2	2185.1	2169.2	2150.4
27.5°	2056.2	2082.0	2111.7	2099.8	2079.0
30°	1942.1	1979.8	2029.4	2019.5	2004.6
32.5°	1834.0	1871.7	1940.1	1936.2	1928.2
35°	1735.8	1759.6	1839.9	1849.9	1842.9
37.5°	1642.6	1664.4	1739.8	1762.6	1756.6
40°	1544.4	1568.2	1627.7	1668.3	1670.3
42.5°	1447.2	1470.0	1518.6	1577.1	1577.1
45°	1344.0	1366.8	1411.4	1475.9	1483.9
47.5°	1242.8	1266.6	1310.3	1374.7	1387.6
50°	1143.6	1165.5	1209.1	1271.6	1291.4
52.5°	1040.5	1064.3	1106.9	1164.5	1193.2
55°	941.3	957.2	1003.8	1059.3	1090.1
57.5°	838.1	853.0	905.6	953.2	984.9
60°	739.0	757.8	798.5	847.1	883.8
62.5°	643.7	663.6	698.3	740.9	782.6
65°	551.5	566.4	600.1	642.7	679.4
67.5°	462.2	475.1	508.8	538.6	577.3
70°	372.0	388.8	413.6	442.4	467.2
72.5°	299.5	306.5	327.3	348.2	373.9
75°	221.2	233.1	250.0	261.9	276.7
77.5°	158.7	165.6	175.6	185.5	199.4
80°	106.1	109.1	118.0	120.0	130.9
82.5°	64.5	66.5	68.4	69.4	73.4
85°	34.7	34.7	34.7	32.7	32.7
87.5°	19.8	19.8	16.9	13.9	9.9
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)