

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P557900

Luminaire Tested: **FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90**

Issue Date: 7/16/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P557900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-257-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90
Description: 4FT FUSL SURFACE MOUNT WITH .156 CLEAR PC FIXTURE SIDE AND .250 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDES
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11123.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.16 / 1.26
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 129.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P557900

CATALOG NUMBER: FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P557900

CATALOG NUMBER: FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 110 | 106 | 102 | 98 | 107 | 103 | 100 | 97 | 99 | 96 | 94 | 95 | 93 | 91 | 92 | 90 | 88 | 86 | | | | | | | | | | | | | | | | | | | |
| 2 | 101 | 93 | 87 | 82 | 98 | 91 | 86 | 81 | 88 | 83 | 79 | 85 | 81 | 77 | 82 | 78 | 75 | 73 | | | | | | | | | | | | | | | | | | | |
| 3 | 92 | 83 | 75 | 69 | 90 | 81 | 74 | 68 | 78 | 72 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 4 | 85 | 74 | 65 | 59 | 83 | 72 | 65 | 59 | 70 | 63 | 58 | 68 | 62 | 57 | 65 | 61 | 56 | 54 | | | | | | | | | | | | | | | | | | | |
| 5 | 78 | 66 | 58 | 51 | 76 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 59 | 54 | 50 | 47 | | | | | | | | | | | | | | | | | | | |
| 6 | 73 | 60 | 51 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 48 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 49 | 44 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 34 | | | | | | | | | | | | | | | | | | | |
| 9 | 59 | 46 | 38 | 33 | 58 | 45 | 38 | 33 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | | | | | | | | | | | | | | | | |
| 10 | 55 | 43 | 35 | 30 | 54 | 42 | 35 | 30 | 41 | 34 | 30 | 40 | 34 | 29 | 39 | 33 | 29 | 28 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|-------|-------|-------|
| 0° | 12945 | 12945 | 12945 |
| 5° | 12979 | 12924 | 12814 |
| 10° | 12841 | 12806 | 12660 |
| 15° | 12614 | 12614 | 12469 |
| 20° | 12346 | 12363 | 12204 |
| 25° | 11940 | 12088 | 11896 |
| 30° | 11243 | 11749 | 11605 |
| 35° | 10624 | 11262 | 11280 |
| 40° | 10108 | 10653 | 10932 |
| 45° | 9530 | 10008 | 10521 |
| 50° | 8920 | 9431 | 10073 |
| 55° | 8228 | 8774 | 9529 |
| 60° | 7410 | 8007 | 8862 |
| 65° | 6543 | 7119 | 8060 |
| 70° | 5452 | 6063 | 6848 |
| 75° | 4285 | 4842 | 5361 |
| 80° | 3064 | 3408 | 3780 |
| 85° | 1998 | 1998 | 1883 |



TEST NUMBER: P557900

CATALOG NUMBER: FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 452.9 | 4.1 |
| 10°-20° | 1272.4 | 11.4 |
| 20°-30° | 1859.3 | 16.7 |
| 30°-40° | 2110.6 | 19.0 |
| 40°-50° | 2037.4 | 18.3 |
| 50°-60° | 1680.7 | 15.1 |
| 60°-70° | 1119.2 | 10.1 |
| 70°-80° | 500.8 | 4.5 |
| 80°-90° | 89.6 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3584.6 | 32.2 |
| 0°-40° | 5695.2 | 51.2 |
| 0°-60° | 9413.3 | 84.6 |
| 0°-90° | 11123.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 11123.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|------|-------|------|-------|------|------|
| 0° | 4810 | 4810 | 4810 | 4810 | 4810 | |
| 5° | 4805 | 4803 | 4784 | 4759 | 4744 | 455 |
| 15° | 4528 | 4539 | 4528 | 4507 | 4476 | 1276 |
| 25° | 4021 | 4053 | 4071 | 4042 | 4006 | 1842 |
| 35° | 3234 | 3278 | 3428 | 3447 | 3434 | 2026 |
| 45° | 2504 | 2547 | 2630 | 2750 | 2765 | 1932 |
| 55° | 1754 | 1783 | 1870 | 1974 | 2031 | 1565 |
| 65° | 1028 | 1055 | 1118 | 1198 | 1266 | 1019 |
| 75° | 412 | 434 | 466 | 488 | 516 | 451 |
| 85° | 65 | 65 | 65 | 61 | 61 | 87 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P557900

CATALOG NUMBER: FUSL-12-4-LD4-3HI-50-UNV-81-96-EDD-90

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° |
|-------|--------|--------|--------|--------|--------|
| 0° | 4810.4 | 4810.4 | 4810.4 | 4810.4 | 4810.4 |
| 2.5° | 4823.3 | 4825.2 | 4814.1 | 4784.5 | 4766.1 |
| 5° | 4804.9 | 4803.0 | 4784.5 | 4758.7 | 4743.9 |
| 7.5° | 4751.3 | 4755.0 | 4749.4 | 4712.5 | 4692.1 |
| 10° | 4699.5 | 4701.4 | 4686.6 | 4657.0 | 4633.0 |
| 12.5° | 4633.0 | 4631.2 | 4610.8 | 4596.0 | 4557.2 |
| 15° | 4527.7 | 4538.8 | 4527.7 | 4507.3 | 4475.9 |
| 17.5° | 4426.0 | 4426.0 | 4433.4 | 4398.3 | 4374.3 |
| 20° | 4311.4 | 4317.0 | 4317.0 | 4289.3 | 4261.5 |
| 22.5° | 4178.4 | 4195.0 | 4200.6 | 4171.0 | 4137.7 |
| 25° | 4021.3 | 4052.7 | 4071.2 | 4041.6 | 4006.5 |
| 27.5° | 3831.0 | 3879.0 | 3934.4 | 3912.3 | 3873.5 |
| 30° | 3618.4 | 3688.7 | 3781.1 | 3762.6 | 3734.9 |
| 32.5° | 3417.0 | 3487.2 | 3614.7 | 3607.3 | 3592.6 |
| 35° | 3234.0 | 3278.4 | 3428.1 | 3446.6 | 3433.6 |
| 37.5° | 3060.3 | 3101.0 | 3241.4 | 3283.9 | 3272.9 |
| 40° | 2877.4 | 2921.7 | 3032.6 | 3108.4 | 3112.1 |
| 42.5° | 2696.3 | 2738.8 | 2829.3 | 2938.4 | 2938.4 |
| 45° | 2504.1 | 2546.6 | 2629.7 | 2749.9 | 2764.6 |
| 47.5° | 2315.6 | 2359.9 | 2441.2 | 2561.4 | 2585.4 |
| 50° | 2130.8 | 2171.4 | 2252.7 | 2369.2 | 2406.1 |
| 52.5° | 1938.6 | 1982.9 | 2062.4 | 2169.6 | 2223.2 |
| 55° | 1753.8 | 1783.3 | 1870.2 | 1973.7 | 2031.0 |
| 57.5° | 1561.6 | 1589.3 | 1687.2 | 1776.0 | 1835.1 |
| 60° | 1376.8 | 1411.9 | 1487.7 | 1578.2 | 1646.6 |
| 62.5° | 1199.4 | 1236.3 | 1301.0 | 1380.5 | 1458.1 |
| 65° | 1027.5 | 1055.2 | 1118.1 | 1197.5 | 1265.9 |
| 67.5° | 861.2 | 885.2 | 948.0 | 1003.5 | 1075.6 |
| 70° | 693.0 | 724.4 | 770.6 | 824.2 | 870.4 |
| 72.5° | 558.1 | 571.0 | 609.8 | 648.7 | 696.7 |
| 75° | 412.1 | 434.3 | 465.7 | 487.9 | 515.6 |
| 77.5° | 295.7 | 308.6 | 327.1 | 345.6 | 371.5 |
| 80° | 197.7 | 203.3 | 219.9 | 223.6 | 243.9 |
| 82.5° | 120.1 | 123.8 | 127.5 | 129.4 | 136.8 |
| 85° | 64.7 | 64.7 | 64.7 | 61.0 | 61.0 |
| 87.5° | 37.0 | 37.0 | 31.4 | 25.9 | 18.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)