

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P277672

Luminaire Tested: **FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P277672  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35269)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84  
Description: FAILSAFE 4 INCH RECESSED LED DOWNLIGHT  
4 INCH LED VANDAL RESISTANT, MEDIUM (50DEGREE BEAM), SPECULAR CLEAR,  
BOTTOM LENS, 0.125 INCH CLEAR POLYCARBONATE  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1249.6 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.76  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P277672

CATALOG NUMBER: FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84

### Luminous Intensity Polar Plot





TEST NUMBER: P277672

CATALOG NUMBER: FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	88	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65
8	82	73	68	64	81	73	67	64	71	67	63	71	66	63	70	66	63	61
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	210502
5°	207697
10°	191438
15°	161381
20°	130609
25°	105209
30°	78348
35°	45337
40°	21808
45°	9086
50°	2992
55°	1352
60°	1027
65°	620
70°	383
75°	507
80°	0
85°	0



TEST NUMBER: P277672

CATALOG NUMBER: FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.6	14.1
10°-20°	395.7	31.7
20°-30°	396.1	31.7
30°-40°	219.3	17.6
40°-50°	51.8	4.1
50°-60°	7.4	0.6
60°-70°	2.8	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.5	77.4
0°-40°	1186.8	95.0
0°-60°	1246.0	99.7
0°-90°	1249.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1249.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1927	
5°	1894	176
15°	1427	396
25°	873	396
35°	340	219
45°	59	52
55°	7	7
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P277672

CATALOG NUMBER: FLD4BX15D010 EU4B1/28040 F4LBXVM1LIBL84

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1926.6
2.5°	1924.3
5°	1893.7
7.5°	1834.9
10°	1725.5
12.5°	1586.7
15°	1426.7
17.5°	1271.5
20°	1123.3
22.5°	986.8
25°	872.7
27.5°	749.2
30°	621.0
32.5°	476.4
35°	339.9
37.5°	230.5
40°	152.9
42.5°	96.4
45°	58.8
47.5°	34.1
50°	17.6
52.5°	9.4
55°	7.1
57.5°	5.9
60°	4.7
62.5°	3.5
65°	2.4
67.5°	2.4
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)