

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P277685

Luminaire Tested: **FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P277685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35269)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86
Description: FAILSAFE 4 INCH RECESSED LED DOWNLIGHT
4 INCH LED VANDAL RESISTANT, MEDIUM (50DEGREE BEAM), SPECULAR CLEAR,
BOTTOM LENS, 0.250 INCH CLEAR POLYCARBONATE
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3336.4 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.76
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277685

CATALOG NUMBER: FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86

Luminous Intensity Polar Plot





TEST NUMBER: P277685

CATALOG NUMBER: FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	88	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65
8	82	73	68	64	81	73	67	64	71	67	63	71	66	63	70	66	63	61
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	562070
5°	554565
10°	511152
15°	430912
20°	348737
25°	280931
30°	209204
35°	121058
40°	58236
45°	24259
50°	8006
55°	3581
60°	2753
65°	1629
70°	990
75°	1309
80°	0
85°	0



TEST NUMBER: P277685

CATALOG NUMBER: FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.9	14.1
10°-20°	1056.7	31.7
20°-30°	1057.7	31.7
30°-40°	585.6	17.6
40°-50°	138.3	4.1
50°-60°	19.8	0.6
60°-70°	7.4	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2583.3	77.4
0°-40°	3169.0	95.0
0°-60°	3327.0	99.7
0°-90°	3336.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3336.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5144	
5°	5056	469
15°	3810	1057
25°	2330	1058
35°	908	586
45°	157	138
55°	19	20
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P277685

CATALOG NUMBER: FLD4BX40D010 EU4B3/58040 F4LBXVM1LIBL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	5144.3
2.5°	5138.0
5°	5056.3
7.5°	4899.3
10°	4607.2
12.5°	4236.6
15°	3809.5
17.5°	3395.0
20°	2999.3
22.5°	2634.9
25°	2330.3
27.5°	2000.5
30°	1658.2
32.5°	1271.9
35°	907.6
37.5°	615.6
40°	408.3
42.5°	257.5
45°	157.0
47.5°	91.1
50°	47.1
52.5°	25.1
55°	18.8
57.5°	15.7
60°	12.6
62.5°	9.4
65°	6.3
67.5°	6.3
70°	3.1
72.5°	3.1
75°	3.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)