

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572226

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 946.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572226

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P572226

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145446
5°	144053
10°	136512
15°	123944
20°	109519
25°	94684
30°	74008
35°	45383
40°	23302
45°	9260
50°	3001
55°	1028
60°	885
65°	698
70°	431
75°	570
80°	0
85°	0



TEST NUMBER: P572226

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.1	11.5
10°-20°	271.5	28.7
20°-30°	315.6	33.4
30°-40°	193.3	20.4
40°-50°	48.0	5.1
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.2	73.6
0°-40°	889.5	94.0
0°-60°	943.1	99.7
0°-90°	946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1184	
5°	1168	109
15°	974	272
25°	698	316
35°	303	193
45°	53	48
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572226

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1183.9
2.5°	1182.7
5°	1168.1
7.5°	1136.7
10°	1094.3
12.5°	1038.6
15°	974.5
17.5°	905.5
20°	837.7
22.5°	769.9
25°	698.5
27.5°	616.2
30°	521.7
32.5°	411.6
35°	302.6
37.5°	213.0
40°	145.3
42.5°	90.8
45°	53.3
47.5°	30.3
50°	15.7
52.5°	7.3
55°	4.8
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)