

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P277671

Luminaire Tested: **FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P277671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35269)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84
Description: FAILSAFE 4 INCH RECESSED LED DOWNLIGHT
4 INCH LED VANDAL RESISTANT, MEDIUM (50DEGREE BEAM), SPECULAR CLEAR,
BOTTOM LENS, 0.125 INCH CLEAR POLYCARBONATE
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 897.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.76
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277671

CATALOG NUMBER: FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84

Luminous Intensity Polar Plot





TEST NUMBER: P277671

CATALOG NUMBER: FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	88	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65
8	82	73	68	64	81	73	67	64	71	67	63	71	66	63	70	66	63	61
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151108
5°	149085
10°	137418
15°	115852
20°	93751
25°	75528
30°	56244
35°	32545
40°	15661
45°	6521
50°	2159
55°	972
60°	743
65°	440
70°	256
75°	338
80°	0
85°	0



TEST NUMBER: P277671

CATALOG NUMBER: FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	14.1
10°-20°	284.1	31.7
20°-30°	284.4	31.7
30°-40°	157.4	17.6
40°-50°	37.2	4.1
50°-60°	5.4	0.6
60°-70°	2.0	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.5	77.4
0°-40°	851.9	95.0
0°-60°	894.5	99.7
0°-90°	897.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1383	
5°	1359	126
15°	1024	284
25°	626	284
35°	244	157
45°	42	37
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P277671

CATALOG NUMBER: FLD4BX10D010 EU4B1/28040 F4LBXVM1LIBL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1383.0
2.5°	1381.3
5°	1359.3
7.5°	1317.1
10°	1238.6
12.5°	1139.0
15°	1024.2
17.5°	912.7
20°	806.3
22.5°	708.4
25°	626.5
27.5°	537.8
30°	445.8
32.5°	341.9
35°	244.0
37.5°	165.5
40°	109.8
42.5°	69.2
45°	42.2
47.5°	24.5
50°	12.7
52.5°	6.8
55°	5.1
57.5°	4.2
60°	3.4
62.5°	2.5
65°	1.7
67.5°	1.7
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)