

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P277679

Luminaire Tested: **FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P277679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35269)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85
Description: FAILSAFE 4 INCH RECESSED LED DOWNLIGHT
4 INCH LED VANDAL RESISTANT, MEDIUM (50DEGREE BEAM), SPECULAR CLEAR,
BOTTOM LENS, 0.187 INCH CLEAR POLYCARBONATE
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2409.7 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.76
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277679

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85

Luminous Intensity Polar Plot





TEST NUMBER: P277679

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	88	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65
8	82	73	68	64	81	73	67	64	71	67	63	71	66	63	70	66	63	61
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	405947
5°	400533
10°	369174
15°	311225
20°	251870
25°	202896
30°	151093
35°	87432
40°	42062
45°	17522
50°	5779
55°	2591
60°	1989
65°	1163
70°	735
75°	971
80°	0
85°	0



TEST NUMBER: P277679

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.7	14.1
10°-20°	763.2	31.7
20°-30°	764.0	31.7
30°-40°	423.0	17.6
40°-50°	99.9	4.1
50°-60°	14.3	0.6
60°-70°	5.3	0.2
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1865.8	77.4
0°-40°	2288.8	95.0
0°-60°	2402.9	99.7
0°-90°	2409.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2409.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3715	
5°	3652	339
15°	2751	763
25°	1683	764
35°	656	423
45°	113	100
55°	14	14
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P277679

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	3715.4
2.5°	3710.9
5°	3651.9
7.5°	3538.5
10°	3327.5
12.5°	3059.9
15°	2751.4
17.5°	2452.0
20°	2166.2
22.5°	1903.1
25°	1683.0
27.5°	1444.9
30°	1197.6
32.5°	918.6
35°	655.5
37.5°	444.6
40°	294.9
42.5°	186.0
45°	113.4
47.5°	65.8
50°	34.0
52.5°	18.1
55°	13.6
57.5°	11.3
60°	9.1
62.5°	6.8
65°	4.5
67.5°	4.5
70°	2.3
72.5°	2.3
75°	2.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)