

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571812

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571812

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P571812

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22568
5°	22654
10°	22729
15°	22728
20°	22605
25°	22068
30°	20626
35°	17862
40°	13953
45°	10007
50°	6498
55°	3898
60°	2285
65°	1453
70°	970
75°	712
80°	566
85°	0



TEST NUMBER: P571812

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.5	6.1
10°-20°	50.4	17.7
20°-30°	74.4	26.1
30°-40°	73.4	25.8
40°-50°	44.9	15.8
50°-60°	17.2	6.0
60°-70°	5.4	1.9
70°-80°	1.6	0.5
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.3	49.9
0°-40°	215.7	75.7
0°-60°	277.8	97.5
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	184	
5°	184	17
15°	179	50
25°	163	74
35°	119	73
45°	58	45
55°	18	17
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P571812

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	183.7
2.5°	184.1
5°	183.7
7.5°	183.3
10°	182.2
12.5°	180.6
15°	178.7
17.5°	176.3
20°	172.9
22.5°	169.0
25°	162.8
27.5°	155.1
30°	145.4
32.5°	133.4
35°	119.1
37.5°	103.3
40°	87.0
42.5°	71.9
45°	57.6
47.5°	44.9
50°	34.0
52.5°	25.1
55°	18.2
57.5°	12.8
60°	9.3
62.5°	7.0
65°	5.0
67.5°	3.9
70°	2.7
72.5°	1.9
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)