

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P277684

Luminaire Tested: **FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P277684  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35269)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86  
Description: FAILSAFE 4 INCH RECESSED LED DOWNLIGHT  
4 INCH LED VANDAL RESISTANT, MEDIUM (50DEGREE BEAM), SPECULAR CLEAR,  
BOTTOM LENS, 0.250 INCH CLEAR POLYCARBONATE  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2381.3 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.76  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P277684

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86

### Luminous Intensity Polar Plot





TEST NUMBER: P277684

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	88	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65
8	82	73	68	64	81	73	67	64	71	67	63	71	66	63	70	66	63	61
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	401173
5°	395817
10°	364836
15°	307560
20°	248905
25°	200509
30°	149327
35°	86405
40°	41562
45°	17321
50°	5711
55°	2553
60°	1967
65°	1163
70°	703
75°	929
80°	0
85°	0



TEST NUMBER: P277684

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	334.7	14.1
10°-20°	754.2	31.7
20°-30°	755.0	31.7
30°-40°	418.0	17.6
40°-50°	98.7	4.1
50°-60°	14.1	0.6
60°-70°	5.2	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1843.9	77.4
0°-40°	2261.8	95.0
0°-60°	2374.6	99.7
0°-90°	2381.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2381.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3672	
5°	3609	335
15°	2719	754
25°	1663	755
35°	648	418
45°	112	99
55°	13	14
65°	4	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P277684

CATALOG NUMBER: FLD4BX30D010 EU4B3/58040 F4LBXVM1LIBL86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3671.7
2.5°	3667.2
5°	3608.9
7.5°	3496.9
10°	3288.4
12.5°	3023.9
15°	2719.0
17.5°	2423.1
20°	2140.7
22.5°	1880.7
25°	1663.2
27.5°	1427.9
30°	1183.6
32.5°	907.8
35°	647.8
37.5°	439.3
40°	291.4
42.5°	183.8
45°	112.1
47.5°	65.0
50°	33.6
52.5°	17.9
55°	13.4
57.5°	11.2
60°	9.0
62.5°	6.7
65°	4.5
67.5°	4.5
70°	2.2
72.5°	2.2
75°	2.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)