

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572652

Luminaire Tested: **FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1521.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572652

CATALOG NUMBER: FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P572652

CATALOG NUMBER: FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	185288
5°	182592
10°	174960
15°	165254
20°	154258
25°	140027
30°	116906
35°	84692
40°	53020
45°	30300
50°	15806
55°	8846
60°	5651
65°	3343
70°	2478
75°	1092
80°	1627
85°	0



TEST NUMBER: P572652

CATALOG NUMBER: FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.8	9.1
10°-20°	364.1	23.9
20°-30°	467.9	30.8
30°-40°	352.0	23.1
40°-50°	141.4	9.3
50°-60°	40.2	2.6
60°-70°	12.7	0.8
70°-80°	3.6	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.7	63.8
0°-40°	1322.7	87.0
0°-60°	1504.3	98.9
0°-90°	1521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1508	
5°	1481	139
15°	1299	364
25°	1033	468
35°	565	352
45°	174	141
55°	41	40
65°	12	13
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P572652

CATALOG NUMBER: FLD4C-20-D010 FEU4C-X-90-40 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1508.2
2.5°	1499.0
5°	1480.6
7.5°	1446.2
10°	1402.5
12.5°	1349.8
15°	1299.3
17.5°	1241.9
20°	1179.9
22.5°	1113.4
25°	1033.0
27.5°	936.5
30°	824.1
32.5°	697.8
35°	564.7
37.5°	440.7
40°	330.6
42.5°	243.3
45°	174.4
47.5°	119.4
50°	82.7
52.5°	57.4
55°	41.3
57.5°	29.9
60°	23.0
62.5°	16.1
65°	11.5
67.5°	9.2
70°	6.9
72.5°	4.6
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)