

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572196

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P572196  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 606.0 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.75  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P572196

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P572196

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93479
5°	91394
10°	84505
15°	75829
20°	66742
25°	57448
30°	46260
35°	30790
40°	16021
45°	7245
50°	3154
55°	2120
60°	1351
65°	959
70°	790
75°	522
80°	0
85°	0



TEST NUMBER: P572196

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	11.3
10°-20°	166.5	27.5
20°-30°	193.3	31.9
30°-40°	128.0	21.1
40°-50°	35.9	5.9
50°-60°	9.0	1.5
60°-70°	3.4	0.6
70°-80°	1.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.5	70.7
0°-40°	556.5	91.8
0°-60°	601.5	99.2
0°-90°	606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	761	
5°	741	69
15°	596	167
25°	424	193
35°	205	128
45°	42	36
55°	10	9
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572196

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	760.9
2.5°	757.6
5°	741.1
7.5°	712.5
10°	677.4
12.5°	637.9
15°	596.2
17.5°	555.5
20°	510.5
22.5°	468.8
25°	423.8
27.5°	381.0
30°	326.1
32.5°	267.9
35°	205.3
37.5°	147.1
40°	99.9
42.5°	64.8
45°	41.7
47.5°	25.3
50°	16.5
52.5°	12.1
55°	9.9
57.5°	7.7
60°	5.5
62.5°	4.4
65°	3.3
67.5°	2.2
70°	2.2
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)