

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572460

Luminaire Tested: **FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1309.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572460

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P572460

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103651
5°	104047
10°	104365
15°	104370
20°	103793
25°	101367
30°	94748
35°	82037
40°	64085
45°	45989
50°	29873
55°	17885
60°	10467
65°	6715
70°	4454
75°	3370
80°	2547
85°	0



TEST NUMBER: P572460

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.3	6.1
10°-20°	231.5	17.7
20°-30°	341.6	26.1
30°-40°	337.1	25.8
40°-50°	206.3	15.8
50°-60°	79.1	6.0
60°-70°	24.7	1.9
70°-80°	7.3	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.5	49.9
0°-40°	990.6	75.7
0°-60°	1276.0	97.5
0°-90°	1309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	844	
5°	844	80
15°	821	232
25°	748	342
35°	547	337
45°	265	206
55°	84	79
65°	23	25
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P572460

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	843.7
2.5°	845.5
5°	843.7
7.5°	842.0
10°	836.6
12.5°	829.5
15°	820.6
17.5°	809.9
20°	793.9
22.5°	776.2
25°	747.8
27.5°	712.2
30°	667.9
32.5°	612.8
35°	547.0
37.5°	474.2
40°	399.6
42.5°	330.4
45°	264.7
47.5°	206.0
50°	156.3
52.5°	115.5
55°	83.5
57.5°	58.6
60°	42.6
62.5°	32.0
65°	23.1
67.5°	17.8
70°	12.4
72.5°	8.9
75°	7.1
77.5°	3.6
80°	3.6
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)