

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572466

Luminaire Tested: **FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1551.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572466

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P572466

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116748
5°	118723
10°	124100
15°	131715
20°	137484
25°	136286
30°	126751
35°	108433
40°	82609
45°	48456
50°	20699
55°	6104
60°	1745
65°	1047
70°	647
75°	854
80°	0
85°	0



TEST NUMBER: P572466

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.9	6.0
10°-20°	293.3	18.9
20°-30°	457.5	29.5
30°-40°	445.2	28.7
40°-50°	222.4	14.3
50°-60°	34.4	2.2
60°-70°	4.2	0.3
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.7	54.4
0°-40°	1288.9	83.1
0°-60°	1545.7	99.7
0°-90°	1551.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1551.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	950	
5°	963	93
15°	1036	293
25°	1005	458
35°	723	445
45°	279	222
55°	28	34
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P572466

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-35 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	950.3
2.5°	953.8
5°	962.7
7.5°	977.0
10°	994.8
12.5°	1017.8
15°	1035.6
17.5°	1049.8
20°	1051.6
22.5°	1039.1
25°	1005.4
27.5°	955.6
30°	893.5
32.5°	815.4
35°	723.0
37.5°	621.7
40°	515.1
42.5°	401.5
45°	278.9
47.5°	179.4
50°	108.3
52.5°	58.6
55°	28.5
57.5°	12.4
60°	7.1
62.5°	5.3
65°	3.6
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)