

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572502

Luminaire Tested: **FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1553.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572502

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P572502

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116895
5°	118883
10°	124250
15°	131880
20°	137654
25°	136462
30°	126907
35°	108568
40°	82721
45°	48526
50°	20737
55°	6104
60°	1745
65°	1047
70°	647
75°	854
80°	0
85°	0



TEST NUMBER: P572502

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	6.0
10°-20°	293.7	18.9
20°-30°	458.1	29.5
30°-40°	445.7	28.7
40°-50°	222.6	14.3
50°-60°	34.5	2.2
60°-70°	4.2	0.3
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.8	54.4
0°-40°	1290.6	83.1
0°-60°	1547.7	99.7
0°-90°	1553.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1553.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	964	93
15°	1037	294
25°	1007	458
35°	724	446
45°	279	223
55°	28	34
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P572502

CATALOG NUMBER: FLD4C-15-D010 FEU4C-X-90-40 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	951.5
2.5°	955.1
5°	964.0
7.5°	978.2
10°	996.0
12.5°	1019.1
15°	1036.9
17.5°	1051.2
20°	1052.9
22.5°	1040.5
25°	1006.7
27.5°	956.9
30°	894.6
32.5°	816.4
35°	723.9
37.5°	622.5
40°	515.8
42.5°	402.0
45°	279.3
47.5°	179.6
50°	108.5
52.5°	58.7
55°	28.5
57.5°	12.5
60°	7.1
62.5°	5.3
65°	3.6
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)