

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572934

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2797.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572934

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P572934

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | 92 | | | | | | | | | | | | | | | | |
| 2 | 106 | 101 | 97 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | | | 84 | | | | | | | | | | | | | | | | |
| 3 | 100 | 93 | 87 | 83 | 98 | 92 | 86 | 82 | 89 | 85 | 81 | 86 | 83 | 80 | 84 | 81 | 78 | 77 | | | 77 | | | | | | | | | | | | | | | | |
| 4 | 94 | 86 | 79 | 75 | 92 | 84 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | 70 | | | | | | | | | | | | | | | | |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | | | 64 | | | | | | | | | | | | | | | | |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 | | | 58 | | | | | | | | | | | | | | | | |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 64 | 59 | 55 | 63 | 59 | 55 | 54 | | | 54 | | | | | | | | | | | | | | | | |
| 8 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 49 | | | 49 | | | | | | | | | | | | | | | | |
| 9 | 69 | 59 | 52 | 48 | 68 | 58 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 45 | | | 45 | | | | | | | | | | | | | | | | |
| 10 | 66 | 55 | 48 | 44 | 65 | 54 | 48 | 44 | 53 | 48 | 44 | 53 | 47 | 44 | 52 | 47 | 43 | 42 | | | 42 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|--------|
| 0° | 210608 |
| 5° | 214187 |
| 10° | 223862 |
| 15° | 237611 |
| 20° | 248023 |
| 25° | 245868 |
| 30° | 228648 |
| 35° | 195599 |
| 40° | 149035 |
| 45° | 87409 |
| 50° | 37346 |
| 55° | 10988 |
| 60° | 3145 |
| 65° | 1860 |
| 70° | 1149 |
| 75° | 1519 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P572934

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 167.6 | 6.0 |
| 10°-20° | 529.1 | 18.9 |
| 20°-30° | 825.4 | 29.5 |
| 30°-40° | 803.1 | 28.7 |
| 40°-50° | 401.1 | 14.3 |
| 50°-60° | 62.1 | 2.2 |
| 60°-70° | 7.5 | 0.3 |
| 70°-80° | 2.1 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1522.1 | 54.4 |
| 0°-40° | 2325.2 | 83.1 |
| 0°-60° | 2788.4 | 99.7 |
| 0°-90° | 2797.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2797.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1714 | |
| 5° | 1737 | 168 |
| 15° | 1868 | 529 |
| 25° | 1814 | 825 |
| 35° | 1304 | 803 |
| 45° | 503 | 401 |
| 55° | 51 | 62 |
| 65° | 6 | 7 |
| 75° | 3 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P572934

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1714.3 |
| 2.5° | 1720.7 |
| 5° | 1736.8 |
| 7.5° | 1762.4 |
| 10° | 1794.5 |
| 12.5° | 1836.1 |
| 15° | 1868.2 |
| 17.5° | 1893.8 |
| 20° | 1897.1 |
| 22.5° | 1874.6 |
| 25° | 1813.8 |
| 27.5° | 1723.9 |
| 30° | 1611.8 |
| 32.5° | 1470.9 |
| 35° | 1304.2 |
| 37.5° | 1121.5 |
| 40° | 929.3 |
| 42.5° | 724.2 |
| 45° | 503.1 |
| 47.5° | 323.6 |
| 50° | 195.4 |
| 52.5° | 105.7 |
| 55° | 51.3 |
| 57.5° | 22.5 |
| 60° | 12.8 |
| 62.5° | 9.6 |
| 65° | 6.4 |
| 67.5° | 6.4 |
| 70° | 3.2 |
| 72.5° | 3.2 |
| 75° | 3.2 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)