

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571716

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P571716  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 251.0 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P571716

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P571716

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	30578
5°	30128
10°	28867
15°	27269
20°	25455
25°	23112
30°	19293
35°	13978
40°	8756
45°	5004
50°	2599
55°	1456
60°	934
65°	552
70°	395
75°	190
80°	283
85°	0



TEST NUMBER: P571716

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.9	9.1
10°-20°	60.1	23.9
20°-30°	77.2	30.8
30°-40°	58.1	23.1
40°-50°	23.3	9.3
50°-60°	6.6	2.6
60°-70°	2.1	0.8
70°-80°	0.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.2	63.8
0°-40°	218.3	87.0
0°-60°	248.3	98.9
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	249	
5°	244	23
15°	214	60
25°	170	77
35°	93	58
45°	29	23
55°	7	7
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P571716

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	248.9
2.5°	247.4
5°	244.3
7.5°	238.6
10°	231.4
12.5°	222.8
15°	214.4
17.5°	204.9
20°	194.7
22.5°	183.7
25°	170.5
27.5°	154.6
30°	136.0
32.5°	115.2
35°	93.2
37.5°	72.7
40°	54.6
42.5°	40.2
45°	28.8
47.5°	19.7
50°	13.6
52.5°	9.5
55°	6.8
57.5°	4.9
60°	3.8
62.5°	2.7
65°	1.9
67.5°	1.5
70°	1.1
72.5°	0.8
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)