

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573156

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2644.0 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573156

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573156

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322085
5°	317408
10°	304150
15°	287265
20°	268144
25°	243414
30°	203227
35°	147232
40°	92167
45°	52678
50°	27465
55°	15400
60°	9804
65°	5814
70°	4310
75°	1899
80°	2830
85°	0



TEST NUMBER: P573156

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.2	9.1
10°-20°	632.9	23.9
20°-30°	813.3	30.8
30°-40°	611.9	23.1
40°-50°	245.8	9.3
50°-60°	69.9	2.6
60°-70°	22.1	0.8
70°-80°	6.3	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1687.5	63.8
0°-40°	2299.4	87.0
0°-60°	2615.0	98.9
0°-90°	2644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2644.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2622	
5°	2574	241
15°	2259	633
25°	1796	813
35°	982	612
45°	303	246
55°	72	70
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P573156

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2621.7
2.5°	2605.7
5°	2573.8
7.5°	2513.9
10°	2438.1
12.5°	2346.4
15°	2258.6
17.5°	2158.8
20°	2051.0
22.5°	1935.4
25°	1795.7
27.5°	1628.0
30°	1432.6
32.5°	1213.0
35°	981.7
37.5°	766.1
40°	574.7
42.5°	423.0
45°	303.2
47.5°	207.6
50°	143.7
52.5°	99.8
55°	71.9
57.5°	51.9
60°	39.9
62.5°	27.9
65°	20.0
67.5°	16.0
70°	12.0
72.5°	8.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)