

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573168

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2197.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573168

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573168

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	338879
5°	331344
10°	306358
15°	274890
20°	241983
25°	208251
30°	167706
35°	111642
40°	58071
45°	26287
50°	11410
55°	7647
60°	4914
65°	3488
70°	2874
75°	1899
80°	0
85°	0



TEST NUMBER: P573168

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.9	11.3
10°-20°	603.7	27.5
20°-30°	700.9	31.9
30°-40°	464.2	21.1
40°-50°	130.2	5.9
50°-60°	32.7	1.5
60°-70°	12.3	0.6
70°-80°	4.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1553.4	70.7
0°-40°	2017.6	91.8
0°-60°	2180.5	99.2
0°-90°	2197.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2197.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2758	
5°	2687	249
15°	2161	604
25°	1536	701
35°	744	464
45°	151	130
55°	36	33
65°	12	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P573168

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2758.4
2.5°	2746.5
5°	2686.8
7.5°	2583.2
10°	2455.8
12.5°	2312.5
15°	2161.3
17.5°	2014.0
20°	1850.9
22.5°	1699.6
25°	1536.3
27.5°	1381.2
30°	1182.2
32.5°	971.2
35°	744.4
37.5°	533.4
40°	362.1
42.5°	234.8
45°	151.3
47.5°	91.6
50°	59.7
52.5°	43.7
55°	35.7
57.5°	27.9
60°	20.0
62.5°	16.0
65°	12.0
67.5°	8.0
70°	8.0
72.5°	4.0
75°	4.0
77.5°	4.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)