

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571818

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 337.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571818

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI

Luminous Intensity Polar Plot



0% Up
100% Dn



TEST NUMBER: P571818

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54																
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25369
5°	25799
10°	26958
15°	28617
20°	29874
25°	29619
30°	27535
35°	23561
40°	17946
45°	10529
50°	4491
55°	1328
60°	369
65°	233
70°	144
75°	190
80°	0
85°	0



TEST NUMBER: P571818

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.2	6.0
10°-20°	63.7	18.9
20°-30°	99.4	29.5
30°-40°	96.7	28.7
40°-50°	48.3	14.3
50°-60°	7.5	2.2
60°-70°	0.9	0.3
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.3	54.4
0°-40°	280.1	83.1
0°-60°	335.8	99.6
0°-90°	337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	206	
5°	209	20
15°	225	64
25°	218	99
35°	157	97
45°	61	48
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571818

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	206.5
2.5°	207.3
5°	209.2
7.5°	212.3
10°	216.1
12.5°	221.1
15°	225.0
17.5°	228.1
20°	228.5
22.5°	225.8
25°	218.5
27.5°	207.6
30°	194.1
32.5°	177.2
35°	157.1
37.5°	135.1
40°	111.9
42.5°	87.2
45°	60.6
47.5°	39.0
50°	23.5
52.5°	12.7
55°	6.2
57.5°	2.7
60°	1.5
62.5°	1.2
65°	0.8
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)