

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573192

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2648.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573192

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573192

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322576
5°	317889
10°	304599
15°	287698
20°	268549
25°	243780
30°	203539
35°	147457
40°	92295
45°	52765
50°	27503
55°	15422
60°	9828
65°	5814
70°	4310
75°	1899
80°	2830
85°	0



TEST NUMBER: P573192

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	9.1
10°-20°	633.8	23.9
20°-30°	814.6	30.8
30°-40°	612.9	23.1
40°-50°	246.1	9.3
50°-60°	70.0	2.6
60°-70°	22.2	0.8
70°-80°	6.3	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1690.0	63.8
0°-40°	2302.9	87.0
0°-60°	2619.0	98.9
0°-90°	2648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2648.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2626	
5°	2578	242
15°	2262	634
25°	1798	815
35°	983	613
45°	304	246
55°	72	70
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P573192

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2625.7
2.5°	2609.7
5°	2577.7
7.5°	2517.7
10°	2441.7
12.5°	2350.0
15°	2262.0
17.5°	2162.1
20°	2054.1
22.5°	1938.3
25°	1798.4
27.5°	1630.5
30°	1434.8
32.5°	1214.9
35°	983.2
37.5°	767.3
40°	575.5
42.5°	423.6
45°	303.7
47.5°	207.9
50°	143.9
52.5°	100.0
55°	72.0
57.5°	52.0
60°	40.0
62.5°	28.0
65°	20.0
67.5°	16.0
70°	12.0
72.5°	8.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)