

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572748

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2012.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572748

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P572748

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159329
5°	159937
10°	160414
15°	160421
20°	159540
25°	155806
30°	145632
35°	126100
40°	98518
45°	70678
50°	45908
55°	27480
60°	16094
65°	10320
70°	6861
75°	5174
80°	3891
85°	0



TEST NUMBER: P572748

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.5	6.1
10°-20°	355.8	17.7
20°-30°	525.1	26.1
30°-40°	518.2	25.8
40°-50°	317.1	15.8
50°-60°	121.6	6.0
60°-70°	38.0	1.9
70°-80°	11.2	0.6
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1004.5	49.9
0°-40°	1522.7	75.7
0°-60°	1961.3	97.5
0°-90°	2012.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2012.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1297	123
15°	1261	356
25°	1149	525
35°	841	518
45°	407	317
55°	128	122
65°	36	38
75°	11	11
85°	0	1
90°	0	



TEST NUMBER: P572748

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-27 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1296.9
2.5°	1299.6
5°	1296.9
7.5°	1294.1
10°	1285.9
12.5°	1275.0
15°	1261.3
17.5°	1244.9
20°	1220.3
22.5°	1193.1
25°	1149.4
27.5°	1094.7
30°	1026.6
32.5°	942.0
35°	840.8
37.5°	728.9
40°	614.3
42.5°	507.8
45°	406.8
47.5°	316.6
50°	240.2
52.5°	177.5
55°	128.3
57.5°	90.1
60°	65.5
62.5°	49.2
65°	35.5
67.5°	27.3
70°	19.1
72.5°	13.7
75°	10.9
77.5°	5.5
80°	5.5
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)