

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573450

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4204.0 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573450

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P573450

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	646344
5°	640193
10°	606640
15°	550772
20°	486685
25°	420759
30°	328900
35°	201703
40°	103521
45°	41125
50°	13360
55°	4605
60°	3956
65°	3140
70°	1940
75°	2563
80°	0
85°	0



TEST NUMBER: P573450

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	484.7	11.5
10°-20°	1206.6	28.7
20°-30°	1402.7	33.4
30°-40°	858.9	20.4
40°-50°	213.3	5.1
50°-60°	24.9	0.6
60°-70°	9.3	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3094.0	73.6
0°-40°	3952.9	94.0
0°-60°	4191.1	99.7
0°-90°	4204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4204.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5261	
5°	5191	485
15°	4330	1207
25°	3104	1403
35°	1345	859
45°	237	213
55°	22	25
65°	11	9
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P573450

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5261.1
2.5°	5255.7
5°	5191.2
7.5°	5051.3
10°	4862.9
12.5°	4615.6
15°	4330.4
17.5°	4023.8
20°	3722.6
22.5°	3421.3
25°	3104.0
27.5°	2738.2
30°	2318.5
32.5°	1829.0
35°	1344.9
37.5°	946.7
40°	645.5
42.5°	403.4
45°	236.7
47.5°	134.5
50°	69.9
52.5°	32.3
55°	21.5
57.5°	16.1
60°	16.1
62.5°	10.8
65°	10.8
67.5°	5.4
70°	5.4
72.5°	5.4
75°	5.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)