

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573228

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2703.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573228

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573228

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329272
5°	324487
10°	310936
15°	293675
20°	274131
25°	248850
30°	207767
35°	150516
40°	94220
45°	53860
50°	28076
55°	15743
60°	10025
65°	5930
70°	4382
75°	1946
80°	2901
85°	0



TEST NUMBER: P573228

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.6	9.1
10°-20°	647.0	23.9
20°-30°	831.5	30.8
30°-40°	625.6	23.1
40°-50°	251.3	9.3
50°-60°	71.4	2.6
60°-70°	22.6	0.8
70°-80°	6.5	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1725.1	63.8
0°-40°	2350.7	87.0
0°-60°	2673.4	98.9
0°-90°	2703.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2703.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2680	
5°	2631	247
15°	2309	647
25°	1836	832
35°	1004	626
45°	310	251
55°	74	71
65°	20	23
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P573228

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2680.2
2.5°	2663.9
5°	2631.2
7.5°	2570.0
10°	2492.5
12.5°	2398.8
15°	2309.0
17.5°	2207.0
20°	2096.8
22.5°	1978.6
25°	1835.8
27.5°	1664.4
30°	1464.6
32.5°	1240.1
35°	1003.6
37.5°	783.2
40°	587.5
42.5°	432.4
45°	310.0
47.5°	212.2
50°	146.9
52.5°	102.0
55°	73.5
57.5°	53.1
60°	40.8
62.5°	28.6
65°	20.4
67.5°	16.3
70°	12.2
72.5°	8.2
75°	4.1
77.5°	4.1
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)