

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573312

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573312  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2515.0 lumens  
Efficiency: N/A  
Efficacy: 53.5 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573312

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P573312

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	387934
5°	379304
10°	350706
15°	314687
20°	277008
25°	238398
30°	191978
35°	127795
40°	66475
45°	30092
50°	13054
55°	8760
60°	5602
65°	3983
70°	3269
75°	2183
80°	0
85°	0



TEST NUMBER: P573312

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.9	11.3
10°-20°	691.1	27.5
20°-30°	802.3	31.9
30°-40°	531.3	21.1
40°-50°	149.0	5.9
50°-60°	37.4	1.5
60°-70°	14.1	0.6
70°-80°	4.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1778.3	70.7
0°-40°	2309.6	91.8
0°-60°	2496.1	99.2
0°-90°	2515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3158	
5°	3076	285
15°	2474	691
25°	1759	802
35°	852	531
45°	173	149
55°	41	37
65°	14	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P573312

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3157.7
2.5°	3144.0
5°	3075.7
7.5°	2957.1
10°	2811.3
12.5°	2647.2
15°	2474.2
17.5°	2305.5
20°	2118.8
22.5°	1945.6
25°	1758.7
27.5°	1581.1
30°	1353.3
32.5°	1111.8
35°	852.1
37.5°	610.6
40°	414.5
42.5°	268.7
45°	173.2
47.5°	104.9
50°	68.3
52.5°	50.1
55°	40.9
57.5°	32.0
60°	22.8
62.5°	18.3
65°	13.7
67.5°	9.1
70°	9.1
72.5°	4.6
75°	4.6
77.5°	4.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)