

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573582

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4685.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573582

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P573582

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	352651
5°	358635
10°	374845
15°	397855
20°	415276
25°	411677
30°	382849
35°	327518
40°	249542
45°	146377
50°	62536
55°	18420
60°	5283
65°	3110
70°	1940
75°	2563
80°	0
85°	0



TEST NUMBER: P573582

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.7	6.0
10°-20°	885.9	18.9
20°-30°	1382.0	29.5
30°-40°	1344.7	28.7
40°-50°	671.7	14.3
50°-60°	104.0	2.2
60°-70°	12.6	0.3
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2548.6	54.4
0°-40°	3893.3	83.1
0°-60°	4668.9	99.7
0°-90°	4685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4685.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2870	
5°	2908	281
15°	3128	886
25°	3037	1382
35°	2184	1345
45°	842	672
55°	86	104
65°	11	13
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P573582

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2870.5
2.5°	2881.2
5°	2908.1
7.5°	2951.1
10°	3004.8
12.5°	3074.4
15°	3128.1
17.5°	3171.1
20°	3176.4
22.5°	3138.8
25°	3037.0
27.5°	2886.6
30°	2698.8
32.5°	2462.9
35°	2183.8
37.5°	1877.8
40°	1556.0
42.5°	1212.7
45°	842.5
47.5°	541.9
50°	327.2
52.5°	177.0
55°	86.0
57.5°	37.6
60°	21.5
62.5°	16.1
65°	10.7
67.5°	10.7
70°	5.4
72.5°	5.4
75°	5.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)