

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573336

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573336  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3069.0 lumens  
Efficiency: N/A  
Efficacy: 65.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573336

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P573336

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	373855
5°	368427
10°	353039
15°	333434
20°	311248
25°	282535
30°	235897
35°	170898
40°	106969
45°	61157
50°	31880
55°	17863
60°	11376
65°	6744
70°	4993
75°	2183
80°	3254
85°	0



TEST NUMBER: P573336

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	280.0	9.1
10°-20°	734.6	23.9
20°-30°	944.1	30.8
30°-40°	710.3	23.1
40°-50°	285.3	9.3
50°-60°	81.1	2.6
60°-70°	25.7	0.8
70°-80°	7.3	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.7	63.8
0°-40°	2669.0	87.0
0°-60°	3035.4	98.9
0°-90°	3069.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3069.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3043	
5°	2988	280
15°	2622	735
25°	2084	944
35°	1140	710
45°	352	285
55°	83	81
65°	23	26
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P573336

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3043.1
2.5°	3024.6
5°	2987.5
7.5°	2918.0
10°	2830.0
12.5°	2723.6
15°	2621.6
17.5°	2505.8
20°	2380.7
22.5°	2246.5
25°	2084.3
27.5°	1889.7
30°	1662.9
32.5°	1408.0
35°	1139.5
37.5°	889.3
40°	667.0
42.5°	491.0
45°	352.0
47.5°	241.0
50°	166.8
52.5°	115.8
55°	83.4
57.5°	60.2
60°	46.3
62.5°	32.4
65°	23.2
67.5°	18.5
70°	13.9
72.5°	9.3
75°	4.6
77.5°	4.6
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)