

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573600

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3017.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573600

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573600

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	465369
5°	455012
10°	420702
15°	377492
20°	332310
25°	285978
30°	230294
35°	153306
40°	79754
45°	36103
50°	15672
55°	10517
60°	6732
65°	4767
70°	3951
75°	2611
80°	0
85°	0



TEST NUMBER: P573600

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.8	11.3
10°-20°	829.0	27.5
20°-30°	962.5	31.9
30°-40°	637.4	21.1
40°-50°	178.8	5.9
50°-60°	44.9	1.5
60°-70°	16.9	0.6
70°-80°	5.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2133.3	70.7
0°-40°	2770.6	91.8
0°-60°	2994.3	99.2
0°-90°	3017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3017.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3788	
5°	3690	342
15°	2968	829
25°	2110	962
35°	1022	637
45°	208	179
55°	49	45
65°	16	17
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P573600

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3788.0
2.5°	3771.5
5°	3689.6
7.5°	3547.3
10°	3372.4
12.5°	3175.6
15°	2968.0
17.5°	2765.7
20°	2541.8
22.5°	2334.0
25°	2109.7
27.5°	1896.7
30°	1623.4
32.5°	1333.7
35°	1022.2
37.5°	732.5
40°	497.3
42.5°	322.4
45°	207.8
47.5°	125.8
50°	82.0
52.5°	60.0
55°	49.1
57.5°	38.4
60°	27.4
62.5°	21.9
65°	16.4
67.5°	11.0
70°	11.0
72.5°	5.5
75°	5.5
77.5°	5.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)