

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573360

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3411.0 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573360

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P573360

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	270106
5°	271137
10°	271965
15°	271977
20°	270484
25°	264140
30°	246877
35°	213791
40°	167013
45°	119829
50°	77846
55°	46586
60°	27273
65°	17500
70°	11638
75°	8781
80°	6580
85°	0



TEST NUMBER: P573360

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.4	6.1
10°-20°	603.3	17.7
20°-30°	890.2	26.1
30°-40°	878.5	25.8
40°-50°	537.6	15.8
50°-60°	206.1	6.0
60°-70°	64.4	1.9
70°-80°	18.9	0.6
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1702.9	49.9
0°-40°	2581.4	75.7
0°-60°	3325.1	97.5
0°-90°	3411.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3411.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2199	
5°	2199	209
15°	2138	603
25°	1949	890
35°	1426	879
45°	690	538
55°	218	206
65°	60	64
75°	18	19
85°	0	3
90°	0	



TEST NUMBER: P573360

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2198.6
2.5°	2203.2
5°	2198.6
7.5°	2194.0
10°	2180.1
12.5°	2161.5
15°	2138.4
17.5°	2110.6
20°	2068.9
22.5°	2022.7
25°	1948.6
27.5°	1856.0
30°	1740.3
32.5°	1596.9
35°	1425.5
37.5°	1235.8
40°	1041.4
42.5°	860.9
45°	689.7
47.5°	536.8
50°	407.3
52.5°	300.9
55°	217.5
57.5°	152.7
60°	111.0
62.5°	83.4
65°	60.2
67.5°	46.3
70°	32.4
72.5°	23.2
75°	18.5
77.5°	9.3
80°	9.3
82.5°	4.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)