

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573378

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3835.0 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573378

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P573378

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	589611
5°	584007
10°	553398
15°	502428
20°	443973
25°	383834
30°	300032
35°	183991
40°	94444
45°	37528
50°	12175
55°	4198
60°	3612
65°	2878
70°	1760
75°	2326
80°	0
85°	0



TEST NUMBER: P573378

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	442.1	11.5
10°-20°	1100.7	28.7
20°-30°	1279.5	33.4
30°-40°	783.5	20.4
40°-50°	194.6	5.1
50°-60°	22.7	0.6
60°-70°	8.5	0.2
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2822.4	73.6
0°-40°	3605.9	94.0
0°-60°	3823.3	99.7
0°-90°	3835.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3835.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4799	
5°	4736	442
15°	3950	1101
25°	2832	1280
35°	1227	784
45°	216	195
55°	20	23
65°	10	8
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573378

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4799.3
2.5°	4794.4
5°	4735.6
7.5°	4607.9
10°	4436.1
12.5°	4210.4
15°	3950.3
17.5°	3670.6
20°	3395.9
22.5°	3121.0
25°	2831.6
27.5°	2497.8
30°	2115.0
32.5°	1668.5
35°	1226.8
37.5°	863.6
40°	588.9
42.5°	368.0
45°	216.0
47.5°	122.7
50°	63.7
52.5°	29.5
55°	19.6
57.5°	14.7
60°	14.7
62.5°	9.9
65°	9.9
67.5°	4.9
70°	4.9
72.5°	4.9
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)