

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573672

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3298.0 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573672

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573672

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	508712
5°	497385
10°	459886
15°	412659
20°	363255
25°	312614
30°	251743
35°	167584
40°	87179
45°	39457
50°	17125
55°	11502
60°	7371
65°	5233
70°	4310
75°	2848
80°	0
85°	0



TEST NUMBER: P573672

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.6	11.3
10°-20°	906.2	27.5
20°-30°	1052.1	31.9
30°-40°	696.8	21.1
40°-50°	195.4	5.9
50°-60°	49.1	1.5
60°-70°	18.5	0.6
70°-80°	6.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.9	70.7
0°-40°	3028.7	91.8
0°-60°	3273.2	99.2
0°-90°	3298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4141	
5°	4033	374
15°	3244	906
25°	2306	1052
35°	1117	697
45°	227	195
55°	54	49
65°	18	18
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P573672

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4140.8
2.5°	4122.8
5°	4033.2
7.5°	3877.7
10°	3686.5
12.5°	3471.3
15°	3244.5
17.5°	3023.3
20°	2778.5
22.5°	2551.4
25°	2306.2
27.5°	2073.4
30°	1774.6
32.5°	1457.9
35°	1117.4
37.5°	800.7
40°	543.6
42.5°	352.4
45°	227.1
47.5°	137.5
50°	89.6
52.5°	65.6
55°	53.7
57.5°	41.9
60°	30.0
62.5°	24.0
65°	18.0
67.5°	12.0
70°	12.0
72.5°	6.0
75°	6.0
77.5°	6.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)