

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573432

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3487.1 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573432

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573432

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276125
5°	277180
10°	278015
15°	278031
20°	276511
25°	270023
30°	252381
35°	218561
40°	170734
45°	122505
50°	79585
55°	47636
60°	27888
65°	17907
70°	11925
75°	8971
80°	6721
85°	0



TEST NUMBER: P573432

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.0	6.1
10°-20°	616.7	17.7
20°-30°	910.1	26.1
30°-40°	898.1	25.8
40°-50°	549.6	15.8
50°-60°	210.7	6.0
60°-70°	65.9	1.9
70°-80°	19.3	0.6
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1740.8	49.9
0°-40°	2638.9	75.7
0°-60°	3399.3	97.5
0°-90°	3487.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3487.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2248	
5°	2248	214
15°	2186	617
25°	1992	910
35°	1457	898
45°	705	550
55°	222	211
65°	62	66
75°	19	19
85°	0	3
90°	0	



TEST NUMBER: P573432

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2247.6
2.5°	2252.3
5°	2247.6
7.5°	2242.8
10°	2228.6
12.5°	2209.7
15°	2186.0
17.5°	2157.6
20°	2115.0
22.5°	2067.8
25°	1992.0
27.5°	1897.3
30°	1779.1
32.5°	1632.5
35°	1457.3
37.5°	1263.3
40°	1064.6
42.5°	880.1
45°	705.1
47.5°	548.8
50°	416.4
52.5°	307.6
55°	222.4
57.5°	156.1
60°	113.5
62.5°	85.3
65°	61.6
67.5°	47.4
70°	33.2
72.5°	23.7
75°	18.9
77.5°	9.5
80°	9.5
82.5°	4.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)