

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573732

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4030.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573732

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573732

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	490922
5°	483795
10°	463579
15°	437855
20°	408713
25°	371011
30°	309763
35°	224410
40°	140471
45°	80303
50°	41857
55°	23454
60°	14939
65°	8837
70°	6573
75°	2895
80°	4316
85°	0



TEST NUMBER: P573732

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.7	9.1
10°-20°	964.6	23.9
20°-30°	1239.7	30.8
30°-40°	932.7	23.1
40°-50°	374.6	9.3
50°-60°	106.5	2.6
60°-70°	33.7	0.8
70°-80°	9.6	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2572.0	63.8
0°-40°	3504.8	87.0
0°-60°	3985.8	98.9
0°-90°	4030.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4030.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3996	
5°	3923	368
15°	3443	965
25°	2737	1240
35°	1496	933
45°	462	375
55°	110	106
65°	30	34
75°	6	10
85°	0	1
90°	0	



TEST NUMBER: P573732

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3996.0
2.5°	3971.7
5°	3923.0
7.5°	3831.7
10°	3716.1
12.5°	3576.4
15°	3442.6
17.5°	3290.4
20°	3126.2
22.5°	2950.0
25°	2737.0
27.5°	2481.5
30°	2183.6
32.5°	1848.9
35°	1496.3
37.5°	1167.7
40°	875.9
42.5°	644.7
45°	462.2
47.5°	316.4
50°	219.0
52.5°	152.1
55°	109.5
57.5°	79.1
60°	60.8
62.5°	42.6
65°	30.4
67.5°	24.3
70°	18.3
72.5°	12.2
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)