

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573540

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3949.0 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573540

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573540

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	312711
5°	313906
10°	314853
15°	314865
20°	313144
25°	305809
30°	285817
35°	247506
40°	193347
45°	138732
50°	90116
55°	53954
60°	31573
65°	20262
70°	13470
75°	10205
80°	7570
85°	0



TEST NUMBER: P573540

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.4	6.1
10°-20°	698.4	17.7
20°-30°	1030.7	26.1
30°-40°	1017.1	25.8
40°-50°	622.4	15.8
50°-60°	238.6	6.0
60°-70°	74.6	1.9
70°-80°	21.9	0.6
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1971.5	49.9
0°-40°	2988.6	75.7
0°-60°	3849.6	97.5
0°-90°	3949.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3949.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2545	
5°	2545	242
15°	2476	698
25°	2256	1031
35°	1650	1017
45°	798	622
55°	252	239
65°	70	75
75°	22	22
85°	0	3
90°	0	



TEST NUMBER: P573540

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2545.4
2.5°	2550.7
5°	2545.4
7.5°	2540.0
10°	2523.9
12.5°	2502.5
15°	2475.6
17.5°	2443.5
20°	2395.2
22.5°	2341.8
25°	2256.0
27.5°	2148.7
30°	2014.8
32.5°	1848.8
35°	1650.3
37.5°	1430.7
40°	1205.6
42.5°	996.7
45°	798.5
47.5°	621.5
50°	471.5
52.5°	348.4
55°	251.9
57.5°	176.8
60°	128.5
62.5°	96.5
65°	69.7
67.5°	53.6
70°	37.5
72.5°	26.8
75°	21.5
77.5°	10.7
80°	10.7
82.5°	5.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)