

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573750

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3945.1 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573750

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P573750

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20								
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90																																				
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																																				
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81																																				
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77																																				
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73																																				
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69																																				
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																																				
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63																																				
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1247233
5°	1122373
10°	870085
15°	629768
20°	436063
25°	317901
30°	230989
35°	136688
40°	57494
45°	17930
50°	2332
55°	1307
60°	1499
65°	1773
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573750

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	800.1	20.3
10°-20°	1369.7	34.7
20°-30°	1088.6	27.6
30°-40°	576.3	14.6
40°-50°	99.3	2.5
50°-60°	7.5	0.2
60°-70°	3.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3258.3	82.6
0°-40°	3834.6	97.2
0°-60°	3941.3	99.9
0°-90°	3945.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3945.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10152	
5°	9101	800
15°	4952	1370
25°	2345	1089
35°	911	576
45°	103	99
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573750

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10152.2
2.5°	9890.8
5°	9101.1
7.5°	8068.4
10°	6974.7
12.5°	5917.6
15°	4951.5
17.5°	4052.3
20°	3335.4
22.5°	2788.6
25°	2345.2
27.5°	1986.7
30°	1628.3
32.5°	1263.7
35°	911.4
37.5°	601.6
40°	358.5
42.5°	206.6
45°	103.2
47.5°	36.5
50°	12.2
52.5°	12.2
55°	6.1
57.5°	6.1
60°	6.1
62.5°	6.1
65°	6.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)