

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573570

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3483.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573570

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P573570

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1101160
5°	990935
10°	768190
15°	556012
20°	384997
25°	280664
30°	203936
35°	120671
40°	50758
45°	15828
50°	2045
55°	1157
60°	1327
65°	1570
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573570

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.4	20.3
10°-20°	1209.3	34.7
20°-30°	961.1	27.6
30°-40°	508.8	14.6
40°-50°	87.6	2.5
50°-60°	6.6	0.2
60°-70°	3.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2876.7	82.6
0°-40°	3385.5	97.2
0°-60°	3479.7	99.9
0°-90°	3483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8963	
5°	8035	706
15°	4372	1209
25°	2070	961
35°	805	509
45°	91	88
55°	5	7
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573570

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8963.2
2.5°	8732.5
5°	8035.3
7.5°	7123.5
10°	6157.9
12.5°	5224.6
15°	4371.6
17.5°	3577.7
20°	2944.8
22.5°	2462.0
25°	2070.5
27.5°	1754.1
30°	1437.6
32.5°	1115.7
35°	804.6
37.5°	531.1
40°	316.5
42.5°	182.4
45°	91.1
47.5°	32.2
50°	10.7
52.5°	10.7
55°	5.4
57.5°	5.4
60°	5.4
62.5°	5.4
65°	5.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)