

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572052

Luminaire Tested: **FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 549.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.87
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572052

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P572052

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84683
5°	82799
10°	76558
15°	68694
20°	60466
25°	52039
30°	41905
35°	27896
40°	14514
45°	6567
50°	2848
55°	1906
60°	1229
65°	872
70°	718
75°	475
80°	0
85°	0



TEST NUMBER: P572052

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.2	11.3
10°-20°	150.9	27.5
20°-30°	175.1	31.9
30°-40°	116.0	21.1
40°-50°	32.5	5.9
50°-60°	8.2	1.5
60°-70°	3.1	0.6
70°-80°	1.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.2	70.7
0°-40°	504.2	91.8
0°-60°	544.9	99.2
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	689	
5°	671	62
15°	540	151
25°	384	175
35°	186	116
45°	38	33
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572052

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-30 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	689.3
2.5°	686.3
5°	671.4
7.5°	645.5
10°	613.7
12.5°	577.9
15°	540.1
17.5°	503.3
20°	462.5
22.5°	424.7
25°	383.9
27.5°	345.1
30°	295.4
32.5°	242.7
35°	186.0
37.5°	133.3
40°	90.5
42.5°	58.7
45°	37.8
47.5°	22.9
50°	14.9
52.5°	10.9
55°	8.9
57.5°	7.0
60°	5.0
62.5°	4.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)