

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573588

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3631.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573588

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573588

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442322
5°	435897
10°	417684
15°	394497
20°	368236
25°	334276
30°	279093
35°	202183
40°	126567
45°	72346
50°	37728
55°	21140
60°	13465
65°	7965
70°	5891
75°	2611
80°	3891
85°	0



TEST NUMBER: P573588

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.3	9.1
10°-20°	869.1	23.9
20°-30°	1117.0	30.8
30°-40°	840.4	23.1
40°-50°	337.5	9.3
50°-60°	96.0	2.6
60°-70°	30.4	0.8
70°-80°	8.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2317.4	63.8
0°-40°	3157.7	87.0
0°-60°	3591.3	98.9
0°-90°	3631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3631.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3600	
5°	3535	331
15°	3102	869
25°	2466	1117
35°	1348	840
45°	416	338
55°	99	96
65°	27	30
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P573588

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3600.4
2.5°	3578.4
5°	3534.6
7.5°	3452.3
10°	3348.2
12.5°	3222.3
15°	3101.7
17.5°	2964.7
20°	2816.6
22.5°	2657.9
25°	2466.0
27.5°	2235.8
30°	1967.4
32.5°	1665.9
35°	1348.1
37.5°	1052.1
40°	789.2
42.5°	580.9
45°	416.4
47.5°	285.1
50°	197.4
52.5°	137.1
55°	98.7
57.5°	71.3
60°	54.8
62.5°	38.4
65°	27.4
67.5°	21.9
70°	16.4
72.5°	11.0
75°	5.5
77.5°	5.5
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)