

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572082

Luminaire Tested: **FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P572082  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 837.0 lumens  
Efficiency: N/A  
Efficacy: 84.8 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.87  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P572082

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P572082

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	128689
5°	127466
10°	120782
15°	109661
20°	96903
25°	83772
30°	65482
35°	40164
40°	20608
45°	8183
50°	2657
55°	921
60°	786
65°	640
70°	395
75°	522
80°	0
85°	0



TEST NUMBER: P572082

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.5	11.5
10°-20°	240.2	28.7
20°-30°	279.3	33.4
30°-40°	171.0	20.4
40°-50°	42.5	5.1
50°-60°	5.0	0.6
60°-70°	1.9	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	616.0	73.6
0°-40°	787.0	94.0
0°-60°	834.4	99.7
0°-90°	837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1048	
5°	1034	96
15°	862	240
25°	618	279
35°	268	171
45°	47	42
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572082

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1047.5
2.5°	1046.4
5°	1033.6
7.5°	1005.7
10°	968.2
12.5°	918.9
15°	862.2
17.5°	801.1
20°	741.2
22.5°	681.2
25°	618.0
27.5°	545.2
30°	461.6
32.5°	364.1
35°	267.8
37.5°	188.5
40°	128.5
42.5°	80.3
45°	47.1
47.5°	26.8
50°	13.9
52.5°	6.4
55°	4.3
57.5°	3.2
60°	3.2
62.5°	2.2
65°	2.2
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)