

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572088

Luminaire Tested: **FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 557.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.87
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572088

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P572088

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85911
5°	84007
10°	77669
15°	69699
20°	61355
25°	52798
30°	42515
35°	28301
40°	14722
45°	6672
50°	2886
55°	1949
60°	1253
65°	872
70°	718
75°	475
80°	0
85°	0



TEST NUMBER: P572088

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	11.3
10°-20°	153.1	27.5
20°-30°	177.7	31.9
30°-40°	117.7	21.1
40°-50°	33.0	5.9
50°-60°	8.3	1.5
60°-70°	3.1	0.6
70°-80°	1.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.9	70.7
0°-40°	511.5	91.8
0°-60°	552.8	99.3
0°-90°	557.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	557.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	699	
5°	681	63
15°	548	153
25°	390	178
35°	189	118
45°	38	33
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572088

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	699.3
2.5°	696.3
5°	681.2
7.5°	654.9
10°	622.6
12.5°	586.3
15°	548.0
17.5°	510.6
20°	469.3
22.5°	430.9
25°	389.5
27.5°	350.2
30°	299.7
32.5°	246.2
35°	188.7
37.5°	135.2
40°	91.8
42.5°	59.5
45°	38.4
47.5°	23.2
50°	15.1
52.5°	11.1
55°	9.1
57.5°	7.1
60°	5.1
62.5°	4.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)