

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236154

Luminaire Tested: **FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT
6" LED Vandal Resistant, Medium (50° Beam), Specular Clear, Bottom lens,
0.125" clear polycarbonate
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 847.1 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236154

CATALOG NUMBER: FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84

Luminous Intensity Polar Plot





TEST NUMBER: P236154

CATALOG NUMBER: FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57588
5°	56799
10°	54170
15°	50609
20°	47273
25°	42853
30°	35053
35°	23981
40°	14274
45°	7732
50°	3816
55°	2332
60°	1566
65°	1050
70°	649
75°	429
80°	639
85°	0



TEST NUMBER: P236154

CATALOG NUMBER: FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	9.6
10°-20°	210.4	24.8
20°-30°	268.1	31.6
30°-40°	189.5	22.4
40°-50°	69.2	8.2
50°-60°	19.2	2.3
60°-70°	6.9	0.8
70°-80°	2.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.6	66.1
0°-40°	749.1	88.4
0°-60°	837.4	98.9
0°-90°	847.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	883	
5°	867	81
15°	749	210
25°	595	268
35°	301	189
45°	84	69
55°	20	19
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P236154

CATALOG NUMBER: FLD6BX10D010 EU6B1/28040 F6LBXVM1LIBL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	882.7
2.5°	879.3
5°	867.3
7.5°	843.4
10°	817.7
12.5°	783.5
15°	749.3
17.5°	715.1
20°	680.9
22.5°	639.8
25°	595.3
27.5°	533.7
30°	465.3
32.5°	383.2
35°	301.1
37.5°	229.2
40°	167.6
42.5°	121.5
45°	83.8
47.5°	56.5
50°	37.6
52.5°	25.7
55°	20.5
57.5°	15.4
60°	12.0
62.5°	8.6
65°	6.8
67.5°	5.1
70°	3.4
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)