

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571920

Luminaire Tested: **FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 554.0 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571920

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P571920

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43871
5°	44039
10°	44174
15°	44172
20°	43928
25°	42903
30°	40104
35°	34720
40°	27119
45°	19459
50°	12633
55°	7561
60°	4423
65°	2849
70°	1904
75°	1424
80°	1061
85°	0



TEST NUMBER: P571920

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	6.1
10°-20°	98.0	17.7
20°-30°	144.6	26.1
30°-40°	142.7	25.8
40°-50°	87.3	15.8
50°-60°	33.5	6.0
60°-70°	10.5	1.9
70°-80°	3.1	0.6
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.6	49.9
0°-40°	419.3	75.7
0°-60°	540.0	97.5
0°-90°	554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	357	
5°	357	34
15°	347	98
25°	316	145
35°	232	143
45°	112	87
55°	35	33
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P571920

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-35 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	357.1
2.5°	357.8
5°	357.1
7.5°	356.3
10°	354.1
12.5°	351.1
15°	347.3
17.5°	342.8
20°	336.0
22.5°	328.5
25°	316.5
27.5°	301.4
30°	282.7
32.5°	259.4
35°	231.5
37.5°	200.7
40°	169.1
42.5°	139.8
45°	112.0
47.5°	87.2
50°	66.1
52.5°	48.9
55°	35.3
57.5°	24.8
60°	18.0
62.5°	13.5
65°	9.8
67.5°	7.5
70°	5.3
72.5°	3.8
75°	3.0
77.5°	1.5
80°	1.5
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)