

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364444

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364444  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS ACRYLIC, CLEAR 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 957.9 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364444

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364444

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	37091
5°	36336
10°	33545
15°	29820
20°	25449
25°	21323
30°	16710
35°	8810
40°	4115
45°	1619
50°	425
55°	114
60°	76
65°	65
70°	56
75°	74
80°	47
85°	94



TEST NUMBER: P364444

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.6	12.8
10°-20°	292.8	30.6
20°-30°	322.1	33.6
30°-40°	177.8	18.6
40°-50°	37.5	3.9
50°-60°	3.1	0.3
60°-70°	0.9	0.1
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.6	77.0
0°-40°	915.4	95.6
0°-60°	956.0	99.8
0°-90°	957.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	957.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1358	
5°	1325	123
15°	1054	293
25°	708	322
35°	264	178
45°	42	38
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364444

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1357.9
2.5°	1347.6
5°	1325.2
7.5°	1274.7
10°	1209.4
12.5°	1134.5
15°	1054.5
17.5°	968.6
20°	875.5
22.5°	790.9
25°	707.5
27.5°	622.6
30°	529.8
32.5°	403.4
35°	264.2
37.5°	175.6
40°	115.4
42.5°	72.8
45°	41.9
47.5°	22.0
50°	10.0
52.5°	4.1
55°	2.4
57.5°	1.7
60°	1.4
62.5°	1.0
65°	1.0
67.5°	0.7
70°	0.7
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)