

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571998

Luminaire Tested: **FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 671.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571998

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P571998

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50505
5°	51364
10°	53692
15°	56980
20°	59473
25°	58966
30°	54828
35°	46913
40°	35747
45°	20971
50°	8964
55°	2635
60°	762
65°	436
70°	287
75°	380
80°	0
85°	0



TEST NUMBER: P571998

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	6.0
10°-20°	126.9	18.9
20°-30°	197.9	29.5
30°-40°	192.6	28.7
40°-50°	96.2	14.3
50°-60°	14.9	2.2
60°-70°	1.8	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.0	54.4
0°-40°	557.6	83.1
0°-60°	668.7	99.7
0°-90°	671.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	671.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	411	
5°	416	40
15°	448	127
25°	435	198
35°	313	193
45°	121	96
55°	12	15
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P571998

CATALOG NUMBER: FLD4C-05-D010 FEU4C-X-90-50 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	411.1
2.5°	412.7
5°	416.5
7.5°	422.7
10°	430.4
12.5°	440.3
15°	448.0
17.5°	454.2
20°	454.9
22.5°	449.6
25°	435.0
27.5°	413.4
30°	386.5
32.5°	352.7
35°	312.8
37.5°	268.9
40°	222.9
42.5°	173.7
45°	120.7
47.5°	77.6
50°	46.9
52.5°	25.4
55°	12.3
57.5°	5.4
60°	3.1
62.5°	2.3
65°	1.5
67.5°	1.5
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)